JŲXQXQXF8

Base Product



Ultra Low Loss (ULL) OM4 MPO8 (Pinned) to MPO8 (Pinned), Fiber Patch Cord, 8-Fiber, Plenum

Product Classification

Regional Availability Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber array cable assembly **Product Brand** Propel | SYSTIMAX ULL

1

Gray

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Connector B, quantity

Connector A, quantity 1

Color, boot A Gray Color, connector A Aqua

Color, boot B

Color, connector B Agua

Stranded **Construction Type**

Furcation Color Agua

Interface, Connector A MPO-08/UPC Male

Interface, Connector B MPO-08/UPC Male

Jacket Color Agua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity Total Fibers, quantity 8

Dimensions


Cable Assembly Length Range (m) 1 - 305

Page 1 of 2

Cable Assembly Length Range (ft)

1 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0° | 4.40 lb @ 90°

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

Classification Agency **ANATEL** Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



Included Products

Fiber indoor cable, LazrSPEED® Plenum MPO Light Duty for Patchcords, 8 fiber, Multimode 760248403 P-008-MP-5K-F20AO OM4, Feet jacket marking, Aqua jacket color

MPO-08, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 2mm 860659018

COMMSCOPE®