760253736 | PPL-DM-16AU-16LC-OM5-SAMPLE



Propel Sample Multimode OM5 MPO-16 Distribution Module, 8 duplex LC to 1X16f MPO, No fiber

- Can be installed and removed from front or rear of panel
- This component requires 4 of the 12 lanes on the Propel Panel blade

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio SYSTIMAX®

Product Type Breakout module

Product Brand Propel
Product Series PPL

General Specifications

Functionality Breakout

Color, front Lime green

Color, rear Gray
Interface, front LC/UPC

Interface Feature, front Internal shutters

Interface, rear MPO

Interface Feature, rear Dust caps

Total Fibers, quantity 0

Total Ports, quantity, front 8

Total Ports, quantity, rear 1

Dimensions

 Height
 11 mm | 0.433 in

 Width
 131 mm | 5.157 in

 Depth
 170 mm | 6.693 in

Optical Specifications

Insertion Loss, maximum dB



760253736 | PPL-DM-16AU-16LC-OM5-SAMPLE

Environmental Specifications

Safety Standard CE | CSA | UL 62368

Packaging and Weights

Packaging quantity 1