

# RT-DF14-4-126

---



High Capacity DUAL Non-Penetrating Roof Frame, 14 ft face, four 2-7/8 in OD x 126 in pipes

## Product Classification

**Product Type** Non-penetrating roof frame  
**Ordering Note** NSTD445 Compliant

## General Specifications

**Mounting** Non-penetrating  
**Pipe, quantity** 4

## Dimensions

**Height** 3,200.4 mm | 126 in  
**Face Width** 4.42 m | 14.5 ft  
**Width** 4,419.6 mm | 174 in  
**Length** 2.377 m | 7.8 ft  
**Pipe Length** 3,200.4 mm | 126 in  
**Face Support Pipe Diameter** 73.152 mm | 2.88 in  
**Pipe Outer Diameter** 73.152 mm | 2.88 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Ballast tray | Frame | Plain end pipes (4)

# RT-DF14-4-126

---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

