

VZWSMART-MSK2 | MEDIUM CROSSOVER PLATE



MEDIUM CROSSOVER PLATE

Medium Crossover Plate, connects 2-3/8" - 2-7/8" pipes to 3-1/2" - 4" pipes

Product Classification

Product Type	Clamp plate
Ordering Note	CommScope® non-standard product

General Specifications

Mounting	Crossover plate
-----------------	-----------------

Dimensions

Mounting Diameter 2, maximum	101.6 mm 4 in
Mounting Diameter 2, minimum	88.9 mm 3.5 in
Mounting Diameter, maximum	73.025 mm 2.875 in
Mounting Diameter, minimum	60.325 mm 2.375 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Environmental Specifications

EPA with 1/2 in (12 mm) radial ice	ft ²
---	-----------------

Packaging and Weights

Included	Plates U-bolts
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

VZWSMART-MSK2 | MEDIUM CROSSOVER PLATE



* Footnotes

EPA with 1/2 in (12 mm) radial ice EPA—Effective Projected Area