## 760254867 | PPL-DM-NULL-8PLC-0M4-BEU



Propel ULL Multimode OM4 MPO-08 front facing breakout module, 4 duplex LC to 1X8f MPO/UPC pinned, Method B Enhanced

- Ultra-low loss (ULL) with Method B Enhanced polarity
- Can be installed and removed from front or rear of panel
- Serialized QR code provides easy access to factory optical test results
- This component requires 3 of the 12 lanes on the Propel Panel blade

#### **Product Classification**

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio SYSTIMAX®

Product Type Breakout module

Product Brand Propel
Product Series PPL

#### General Specifications

**Functionality** Breakout

Color, front Aqua | Gray
Interface, front LC/UPC + MPO

Interface Feature, front Internal shutters | MPO Pinned

**Polarity** Method B Enhanced (ULL)

Total Fibers, quantity 8

Total Ports, quantity, front 5

Total Ports, quantity, rear 0

#### Dimensions

 Height
 11 mm | 0.433 in

 Width
 65 mm | 2.559 in

 Depth
 170 mm | 6.693 in

### Optical Specifications

**Fiber Mode** Multimode

Fiber Type OM4
Insertion Loss, maximum 0.35 dB

Page 1 of 2



# 760254867 | PPL-DM-NULL-8PLC-OM4-BEU

### **Environmental Specifications**

**Qualification Standards** IEC 61753-1 | TIA-568.3-D

Safety Standard UL 62368

Packaging and Weights

Packaging quantity 1

**Weight, net** 0.109 kg | 0.24 lb

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

