

1499539-1 | TE610UC-WT250



Undercarpet Copper Cable, category 6, 4-pair, 8 conductors, unshielded, 250 ft, white

- Exceeds TIA/EIA and ISO specifications for Categories specified
- Exceeds all requirements for Gigabit Ethernet
- Leadfree jacketing

OBSOLETE

This product was discontinued on: December 31, 2022

Product Classification

Regional Availability	North America
Portfolio	NETCONNECT®
Product Type	Twisted pair cable
Product Series	Undercarpet

General Specifications

ANSI/TIA Category	6
Cable Type	U/UTP (unshielded)
Jacket Color	White
Pairs, quantity	4
Supported Application	Commercial Office Retail
Transmission Standards	ANSI/TIA-568.2-D

Dimensions

Cable Length	76.2 m 250 ft
Conductor Gauge, singles	24 AWG

Electrical Specifications

Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

1499539-1 | TE610UC-WT250

Safety Voltage Rating 300 V

Material Specifications

Conductor Material Bare copper

Environmental Specifications

Safety Standard UL

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

