

CLT5DM-CO



MQ Multiport cluster 5 ports cable assembly with interface type MQ female to 7/16DIN male, size 1/4"

Product Classification

Product Type	Wireless transmission cable assembly
Product Series	MQ
Warranty	Two years

General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	MQ Female
Interface, Connector B	7-16 DIN Male
Specification Sheet Revision Level	A

Dimensions

Nominal Size	1/4 in
---------------------	--------

Port Configuration

Pin Assignment	Label
1	MQ5-1 (R+)
2	MQ5-2 (CR+)
3	MQ5-3 (CL+)
4	MQ5-4 (L+)
5	MQ5-5 (CAL)

Mechanical Specifications

CLT5DM-CO

Minimum Bend Radius, multiple Bends	25.4 mm 1 in
Minimum Bend Radius, single Bend	25.4 mm 1 in

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Immersion Test Method	IEC 60529, IP67

* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines
-----------------	--