LSF2-50 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, with Integrated Birdproofing Shell 2m

• WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type		SureFlex® Premium, static PIM	
Product Brand		HELIAX® SureFlex®	
Product Series		LSF2-50	
General Specifications			
Body Style, Connector A		Straight	
Body Style, Connector B		Straight	
Interface, Connector A		4.3-10 Male	
Interface, Connector B		4.3-10 Male	
Specification Sheet Revision Level		А	
Dimensions			
Length		2 m 6.562 ft	
Nominal Size		3/8 in	
Electrical Specifications			
3rd Order IMD		-119 dBm	
3rd Order IMD Test Method		Two +43 dBm carriers	
VSWR/Return Loss			
Fraguanay Pand	Vewd	Poturn Loco	

Frequency Band	VSWR	Return Loss (dB)
698–970 MHz	1.065	30
1700–2200 MHz	1.065	30
2200–2700 MHz	1.083	28
3400-3800 MHz	1.222	20

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: April 5, 2023



LS2-HMHM-2M-PB

3800-6000 MHz

1.222

20

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: April 5, 2023

