

LMR-195 Jumper with interface types N Male and SMA Male, 3 m



Product Classification

Product Type Coaxial wireless cable

General Specifications

Body Style, Connector A Straight

Body Style, Connector B Straight

Interface, Connector A N Male

Interface, Connector B SMA Male

Specification Sheet Revision Level A

Dimensions

Length 3 m | 9.843 ft

Nominal Size 0.195 in

VSWR /Return Loss

Frequency Band	VSWR	Return Loss (dB)	Insertion Loss (dB)	VSWR, typical	Return Loss, typical (dB)	Insertion Loss, typical (dB)
0–3000 MHz	1.222	20	1.8	1.184	21.5	1.61

Mechanical Specifications

Minimum Bend Radius, multiple Bends 63.5 mm | 2.5 in

Minimum Bend Radius, single Bend 19.1 mm | 0.752 in

Packaging and Weights

7855829

Weight, gross 0.21 kg | 0.463 lb

Weight, net 0.19 kg | 0.419 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

ROHS

UK-ROHS

Classification

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted

Compliant/Exempted

