



ReadyPATCH® ULL Singlemode MPO-12 Distribution Module, 6 duplex LC non-keyed red adapters to 1X12f MPO/UPC non-pinned, Method B Enhanced

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Breakout module
Product Brand	ReadyPATCH®

General Specifications

Functionality	Breakout
Adapters, quantity, front	6
Adapters, quantity, rear	1
Color, front	Red
Color, rear	Black
Data Module Type	Standard
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	MPO Non-Pinned
Polarity	Method B Enhanced (ULL)
Shuttered	No
Total Fibers, quantity	12
Total Ports, quantity, front	6

Dimensions

Height	27.94 mm 1.1 in
Width	129.54 mm 5.1 in
Depth	127 mm 5 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	0.6 dB

Environmental Specifications

Safety Standard	UL
------------------------	----

Packaging and Weights

Packaging quantity	1
---------------------------	---