


# MC-CP12M-12-96-J

---



3-Sector Adjustable Monopole Co-location Platform Kit, 15 in to 50 in OD, 12 ft 6 in face, includes twelve 96 in pipes

## Product Classification

**Product Type** Co-location platform

## General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD

**Pipe, quantity** 12

**Sectors, quantity** 3

## Dimensions

**Height** 2,438.4 mm | 96 in

**Face Width** 3.81 m | 12.5 ft

**Width** 3810 mm | 150 in

**Pipe Length** 2,438.4 mm | 96 in

**Face Support Pipe Diameter** 73.152 mm | 2.88 in

**Mounting Diameter, maximum** 1270 mm | 50 in

**Mounting Diameter, minimum** 381 mm | 15 in

**Pipe Outer Diameter** 60.452 mm | 2.38 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Plain end pipes (12) | Platform | Rail | Ring mount

**Packaging quantity** 1

# MC-CP12M-12-96-J

---

**Weight, net**

791.7 kg | 1,745.4 lb