

F-CLAMP-A-1B



KwikClamp™ Hanger for power & fiber cables, 4.5-9 mm, single stack, round or flat mounting; includes hardware

Product Classification

| | |
|----------------------|--|
| Product Type | Hanger kit |
| Product Brand | KwikClamp™ |
| Ordering Note | CommScope® standard product in Europe, the Middle East, and Africa |

General Specifications

| | |
|--------------------------|---|
| Cables per Hanger | 1 |
| Color | Black |
| Hanger Type | KwikClamp™ hanger |
| Mounting | 3-25 mm flat plate Round Member 8-25 mm |

Dimensions

| | |
|--|-------------------|
| Maximum Stack Height | 1 |
| Height | 116 mm 4.567 in |
| Width | 32 mm 1.26 in |
| Length | 46 mm 1.811 in |
| Compatible Cable Diameter Range | 4.5-9 mm |
| Compatible Diameter, maximum | 9 mm 0.354 in |
| Compatible Diameter, minimum | 4.5 mm 0.177 in |
| Hanger Spacing, maximum | 1.83 m 6.004 ft |

Electrical Specifications

| | |
|------------------------------------|--------|
| Return Loss Effect, maximum | 0.1 dB |
| DTF Effect, maximum | 0.1 dB |

F-CLAMP-A-1B

Material Specifications

Material Type EPDM rubber | Engineered plastic | Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

UV Resistance, minimum with no degradation ≥124 hours exposure in accelerated UV life chamber, testing duration 1344 hrs

Packaging and Weights

Height, packed 15.5 cm | 6.102 in

Width, packed 30.5 cm | 12.008 in

Length, packed 35.5 cm | 13.976 in

Included Hardware

Packaging quantity 90

Weight, gross 9.87 kg | 21.76 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power