

# F-CLAMP-B-2B

---



KwikClamp™ Hanger for power & fiber cables, 7-22 mm, double stack, round or flat mounting; includes hardware

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	KwikClamp™
<b>Ordering Note</b>	CommScope® standard product in Europe, the Middle East, and Africa

## General Specifications

<b>Cables per Hanger</b>	1
<b>Color</b>	Black
<b>Hanger Type</b>	KwikClamp™ hanger
<b>Mounting</b>	3-25 mm flat plate   Round Member 8-25 mm

## Dimensions

<b>Maximum Stack Height</b>	2
<b>Height</b>	162 mm   6.378 in
<b>Width</b>	32 mm   1.26 in
<b>Length</b>	42 mm   1.654 in
<b>Compatible Cable Diameter Range</b>	7-22 mm
<b>Compatible Diameter, maximum</b>	22 mm   0.866 in
<b>Compatible Diameter, minimum</b>	7 mm   0.276 in
<b>Hanger Spacing, maximum</b>	1.83 m   6.004 ft

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

# F-CLAMP-B-2B

---

## Material Specifications

**Material Type** EPDM rubber | Engineered plastic | Stainless steel

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Five times cable weight

**UV Resistance, minimum with no degradation** ≥124 hours exposure in accelerated UV life chamber, testing duration 1344 hrs

## Packaging and Weights

**Height, packed** 15.5 cm | 6.102 in

**Width, packed** 30.5 cm | 12.008 in

**Length, packed** 35.5 cm | 13.976 in

**Included** Hardware

**Packaging quantity** 48

**Weight, gross** 7.1 kg | 15.653 lb

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power