

# F-CLAMP-B2-3B

---



KwikClamp™ Hanger for power & fiber cables, two 7-22 mm holes (alongside each other), triple block; includes hardware

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	KwikClamp™
<b>Ordering Note</b>	CommScope® standard product in Europe, the Middle East, and Africa

## General Specifications

<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Hanger Type</b>	KwikClamp™ hanger
<b>Mounting</b>	3–25 mm flat plate   Round Member 8-25 mm

## Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	204 mm   8.032 in
<b>Width</b>	56 mm   2.205 in
<b>Length</b>	46 mm   1.811 in
<b>Compatible Cable Diameter Range</b>	7-22 mm
<b>Compatible Diameter, maximum</b>	22 mm   0.866 in
<b>Compatible Diameter, minimum</b>	7 mm   0.276 in
<b>Hanger Spacing, maximum</b>	1.83 m   6.004 ft

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Engineered plastic   Stainless steel
----------------------	--------------------------------------

## Mechanical Specifications

# F-CLAMP-B2-3B

---

**Vibration Survival**

≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature**

-40 °C to +70 °C (-40 °F to +158 °F)

**Corrosion Resistance, minimum with no degradation**

≥500 hours in salt spray chamber

**Environmental Strength Capability**

Five times cable weight

**UV Resistance, minimum with no degradation**

≥124 hours exposure in accelerated UV life chamber, testing duration 1344 hrs

## Packaging and Weights

**Height, packed**

15.5 cm | 6.102 in

**Width, packed**

30.5 cm | 12.008 in

**Length, packed**

35.5 cm | 13.976 in

**Included**

Hardware

**Packaging quantity**

18

**Weight, gross**

5.149 kg | 11.352 lb

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power