# 64624447-06 | 0-006-LD-8M-M12BL/20G/PE/PA



Outdoor Fiber Cable, 6-fiber, singlemode OS2, loose tube, blue

#### **Product Classification**

Regional Availability Australia/New Zealand

Portfolio CommScope®
Product Type Fiber OSP cable

Product Series O-LD

### General Specifications

Cable TypeLoose tubeSubunit TypeGel-filledJacket ColorBlueJacket MarkingMeters

Fibers per Subunit, quantity 6

Total Fiber Count 6

**Dimensions** 

**Diameter Over Jacket** 8.9 mm | 0.35 in

Material Specifications

Jacket Material Nylon

Mechanical Specifications

Flex 25 cycles

Optical Specifications

Fiber Type G.652.D | OS2

Optical Specifications, Wavelength Specific

Standards Compliance TIA-492CAAB (OS2)



# 64624447-06 | 0-006-LD-8M-M12BL/20G/PE/PA

## **Environmental Specifications**

**Operating Temperature**  $-10 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \text{ (+14 } ^{\circ}\text{F to } +158 \, ^{\circ}\text{F)}$ 

Environmental Space Buried

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

