



OCC1P Wideband Splitter, planar, singlemode, 1x32, symmetrical split ratio, 0,9 mm cable, medium duty housing

Product Classification

Regional Availability	Asia
Product Type	Splitter component
Product Series	OCC1P

General Specifications

Device Type	Component, rectangular
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Application	For use in FOSC closures
Circuits, quantity	1
Distribution Type	1 x 32 splitter
Interface, Input	Stub tail
Interface, Output	Stub tail
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Pigtail Length, Input	2.5 m 8.202 ft
Pigtail Length, Output	2.5 m 8.202 ft
Pigtail Diameter, Input	0.9 mm 0.035 in
Pigtail Diameter, Output	0.9 mm 0.035 in

Environmental Specifications

Qualification Standards	Telcordia GR-1209-CORE Telcordia GR-1221-CORE
-------------------------	---

Packaging and Weights

760239444 | OCC1P-13200-NNSES2SEB

Packaging quantity 1