

TES-SS-MSK14 | UNIVERSAL ADJUSTABLE CROSSOVER



Universal Crossover Plate,Round - joins range of 2-3/8 up to to 3-1/2 in OD round members

Product Classification

Product Type Clamp plate

General Specifications

Mounting Crossover plate

Dimensions

Height 5.5 in | 139.7 mm

Width 5.5 in | 139.7 mm

Length 10.5 in | 266.7 mm

Mounting Diameter 2, maximum 3.5 in | 88.9 mm

Mounting Diameter 2, minimum 2.4 in | 60.96 mm

Mounting Diameter, maximum 3.5 in | 88.9 mm

Mounting Diameter, minimum 2.4 in | 60.96 mm

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Hardware | Plates

Packaging quantity 1

Weight, net 5 kg | 11.023 lb