



ReadyPATCH® ULL Multimode OM5 MPO-12 Distribution Module, 6 duplex LC non-keyed green adapters to 1X12f MPO/UPC non-pinned, Method B Enhanced

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module
<b>Product Brand</b>	ReadyPATCH®

## General Specifications

<b>Functionality</b>	Breakout
<b>Adapters, quantity, front</b>	6
<b>Adapters, quantity, rear</b>	1
<b>Color, front</b>	Green
<b>Color, rear</b>	Gray
<b>Data Module Type</b>	Standard
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	MPO Non-Pinned
<b>Polarity</b>	Method B Enhanced (ULL)
<b>Shuttered</b>	No
<b>Total Fibers, quantity</b>	12
<b>Total Ports, quantity, front</b>	6

## Dimensions

<b>Height</b>	27.94 mm   1.1 in
<b>Width</b>	129.54 mm   5.1 in
<b>Depth</b>	127 mm   5 in

## Optical Specifications

<b>Fiber Mode</b>	Multimode
-------------------	-----------

<b>Fiber Type</b>	OM5, LazrSPEED® wideband
<b>Insertion Loss, maximum</b>	0.35 dB

## Environmental Specifications

<b>Safety Standard</b>	c-UL-us
------------------------	---------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---