

FT-24CGAHBN



HELIAX® Modular Fiber Cable assembly, 24 single mode fibers, assembly, 24 single mode fibers, End 1: HMFOC 12 fibers; End 2: DLC GEN 1.5; LSZH cable. Anti-rodent with E-Glass Protection.

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Wireless Fiber Cable Assemblies
Product Series	FT
Ordering Note	CommScope® Standard Product in Europe

General Specifications

Construction Type	Fiber modular
Interface, Connector A	HMFOC
Interface Feature, connector A	Standard
Interface Body Style, connector A	Straight
Interface, Connector B	DLC GEN 1.5
Interface Feature, connector B	Standard
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	12

Dimensions

Cable Assembly Length Range (m)	1 – 10
Diameter Over Jacket	8.9 mm 0.35 in

Mechanical Specifications

Minimum Bend Radius	75 mm 2.953 in
Minimum Bend Radius, furcation	10 mm 0.394 in

Optical Specifications

Fiber Type	G.657.A2
Insertion Loss, typical note	Insertion loss is measured at 1310 and 1550 nm

FT-24CGAHBN

Insertion Loss, typical 0.5

Environmental Specifications

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Environmental Space Indoor | Outdoor

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)