

TB-COMP-KIT



Connector Attachment Tool Kit, includes tool box

OBSOLETE

Product Classification

Product Type	Tool
Ordering Note	CommScope® non-standard product

General Specifications

Application	Prepare various coaxial cables for connector attachment
Tool Type	Tool kit

Packaging and Weights

Height, packed	444.5 mm 17.5 in
Width, packed	264.16 mm 10.4 in
Length, packed	190.5 mm 7.5 in
Packaging quantity	1
Weight, gross	4.08 kg 8.995 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

TB-COMP-KIT

224354	-	Ruler, 6 in (152.4 mm)
224356	-	Point File
224363	-	Flare Tool for 1/2 in coaxial cable
224368	-	Flare Tool for 7/8 in coaxial cable
MCPT-1412	-	EASIAx® Manual Cable Preparation Tool for FSJ1-50A and FSJ4-50B coaxial cable
MCPT-78	-	EASIAx® Manual Cable Preparation Tool for 7/8 in coaxial cable
MCPT-A5-D	-	Manual Cable Preparation Tool for 7/8 in coaxial cable and A5 Connectors
MCPT-L5-S	-	Manual Cable Preparation Tool for 7/8 in coaxial cable LDF5 connectors

224354

Ruler, 6 in (152.4 mm)



Product Classification

Product Type	Tool
Ordering Note	CommScope® non-standard product

General Specifications

Application	Measuring tool
Tool Type	Measuring tool

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Packaging and Weights

Height, packed	304.8 mm 12 in
Width, packed	40.64 mm 1.6 in
Length, packed	22.86 mm 0.9 in
Packaging quantity	1
Weight, gross	0.54 kg 1.19 lb

Point File



Product Classification

Product Type	Tool
Ordering Note	CommScope® non-standard product

General Specifications

Application	Hand tool to shape material by abrasion
Tool Type	File

Material Specifications

Material Type	Steel
----------------------	-------

Packaging and Weights

Height, packed	149.86 mm 5.9 in
Width, packed	50.8 mm 2 in
Length, packed	50.8 mm 2 in
Packaging quantity	1
Weight, gross	0.04 kg 0.088 lb

Flare Tool for 1/2 in coaxial cable



Product Classification

Product Type	Tool
Ordering Note	CommScope® standard product in Asia Pacific CommScope® standard product in Europe, the Middle East, and Africa

General Specifications

Application	Separates foam from outer conductor of coaxial cable
Tool Type	Flare tool

Dimensions

Nominal Size	1/2 in
---------------------	--------

Material Specifications

Material Type	Steel Wood
----------------------	--------------

Packaging and Weights

Height, packed	152.4 mm 6 in
Width, packed	50.8 mm 2 in
Length, packed	50.8 mm 2 in
Packaging quantity	1
Weight, gross	0.15 kg 0.331 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



224368

Flare Tool for 7/8 in coaxial cable



Product Classification

Product Type	Tool
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa

General Specifications

Application	Separates foam from outer conductor of coaxial cable
Tool Type	Flare tool

Dimensions

Nominal Size	7/8 in
---------------------	--------

Material Specifications

Material Type	Steel Wood
----------------------	--------------

Packaging and Weights

Height, packed	152.4 mm 6 in
Width, packed	50.8 mm 2 in
Length, packed	50.8 mm 2 in
Packaging quantity	1
Weight, gross	0.15 kg 0.331 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



MCPT-1412



EASIAX® Manual Cable Preparation Tool for FSJ1-50A and FSJ4-50B coaxial cable

Product Classification

Product Type	Tool
Product Brand	EASIAX Plus®
Ordering Note	CommScope® standard product (Global)

General Specifications

Application	Prepares cable for connector attachment
Cutting Blade Life	25 cable preparations
Cutting Blades Included	1
Jacket Blades Included	1
Tool Type	Manual cable preparation tool

Dimensions

Nominal Size	1/2 in 1/4 in
---------------------	-----------------

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Packaging and Weights

Height, packed	93.98 mm 3.7 in
Width, packed	76.2 mm 3 in
Length, packed	50.8 mm 2 in
Packaging quantity	1
Weight, gross	0.27 kg 0.595 lb

Regulatory Compliance/Certifications

MCPT-1412

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS



Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

MCPT-78



EASIAx® Manual Cable Preparation Tool for 7/8 in coaxial cable

Product Classification

Product Type	Tool
Product Brand	EASIAx Plus®
Ordering Note	CommScope® standard product (Global)

General Specifications

Application	Prepares cable for connector attachment
Cutting Blade Life	25 cable preparations
Cutting Blades Included	1
Jacket Blades Included	1
Tool Type	Manual cable preparation tool

Dimensions

Nominal Size	7/8 in
---------------------	--------

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Packaging and Weights

Height, packed	93.98 mm 3.7 in
Width, packed	76.2 mm 3 in
Length, packed	50.8 mm 2 in
Packaging quantity	1
Weight, gross	0.25 kg 0.551 lb

Regulatory Compliance/Certifications

MCPT-78

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS



Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

MCPT-A5-D



Manual Cable Preparation Tool for 7/8 in coaxial cable and A5 Connectors

Product Classification

Product Type	Tool
Ordering Note	CommScope® standard product (Global)

General Specifications

Application	Prepares cable for connector attachment
Cutting Blade Life	500 cable preparations
Cutting Blades Included	4
Jacket Blades Included	2
Tool Type	Manual cable preparation tool

Dimensions

Nominal Size	7/8 in
---------------------	--------

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Packaging and Weights

Height, packed	101.6 mm 4 in
Width, packed	127 mm 5 in
Length, packed	177.8 mm 7 in
Packaging quantity	1
Weight, gross	0.27 kg 0.595 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

MCPT-A5-D

REACH-SVHC


Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant



MCPT-L5-S



Manual Cable Preparation Tool for 7/8 in coaxial cable LDF5 connectors

Product Classification

Product Type	Tool
Ordering Note	CommScope® standard product (Global)

General Specifications

Application	Prepares cable for connector attachment
Cutting Blade Life	500 cable preparations
Cutting Blades Included	4
Jacket Blades Included	2
Tool Type	Manual cable preparation tool

Dimensions

Nominal Size	7/8 in
---------------------	--------

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Packaging and Weights

Height, packed	101.6 mm 4 in
Width, packed	127 mm 5 in
Length, packed	177.8 mm 7 in
Packaging quantity	1
Weight, gross	0.27 kg 0.595 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

MCPT-L5-S

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

