

Braided Cable and Connector Solutions for EMEA, APAC and CALA regions

FEATURES AND BENEFITS

- Specified: By all major OEMs
- **Designed to Flex**: Tight bend radius equals exceptional flexibility
- Engineered to Perform: Low attenuation at every frequency
- **High-quality RF Signal**: Reliability of factory testing reports





CNT Cable Portfolio

CNT Cable Family	Standard	Standard Low Braided	Fire retardant	
CNT-300	CNT-300A-300M	CNT 200A LD COOM	CNT-300A-FR-300M	
	CNT-300A-600M	CNT-300A-LB-600M	CNT-300A-FR-600M	
CNT-400	CNT-400-300M		CNT-400-FR-300M	
	CNT-400-500M		CNT-400-FR-500M	

CNT Connector Portfolio

CNT Cable Family	Connector Type	Interface	7–16	N-Type	TNC	SMA	4.3-10
CNT-300	Crimp	Male		300APNM-CS8			
	Clamp	Male		300BPNM-C	300PTM-C		
		Right Angle Male		300BPNR-C	300BPTR-C		
CNT-400	Crimp	Male		400BPNM-C-CR 400APNM-CS8		400PSM-CR	400PHM-C-CR
		Right Angle Male	400PDR-CR	400BPNR-C-CR			
		Female		400BPNF-C-CR	400BPTF-C-CR		
	Clamp	Male	400BPDM-C	400BPNM-C	400BPNM-C		
		Right Angle Male		400BPNR-C	400BPTR-C		
		Female		400BPNF-C	400BPTF-C		

CNT Cable /Accessory Matrix

	Cable Prep Tool	Snap-in Hanger	Hanger Block	Hardware for Block Hanger	Hardware for Block Hanger	Grounding Kit	Weatherproofing
CNT-300	BCPT-3400	SSH-710	68MCLICK	252029-10KT-P	252026-10KT-P	GK-SUNV	WK-CNT
CNT-400		SSH-1014	912MCLICK	252029-10KT-P	252026-10KT-P		

^{*}CNT products are not available in North America

commscope.com

 $\label{thm:condition} \mbox{Visit our website or contact your local CommScope representative for more information.}$

© 2024 CommScope, Inc. All rights reserved.

CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners.