

Heat Treated LDF2RK-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 3/8 in, black non-halogenated, fire retardant polyolefin jacket

Product Classification

 Product Type
 Coaxial wireless cable

 Product Brand
 HELIAX® | SureFlex®

Product Series LDF2-50

General Specifications

Flexibility Standard

Jacket Color Black

Performance Note Attenuation values typical, guaranteed within 5%

Dimensions

 Diameter Over Dielectric
 8.636 mm | 0.34 in

 Diameter Over Jacket
 11.176 mm | 0.44 in

 Inner Conductor OD
 3.048 mm | 0.12 in

 Outer Conductor OD
 9.652 mm | 0.38 in

Nominal Size 3/8 in

Electrical Specifications

Cable Impedance 50 ohm ±1 ohm

Capacitance 75 pF/m | 22.86 pF/ft

dc Resistance, Inner Conductor3.478 ohms/km | 1.06 ohms/kftdc Resistance, Outer Conductor2.854 ohms/km | 0.87 ohms/kft

dc Test Voltage 2500 V

Inductance $0.19 \, \mu H/m \, \mid \, 0.058 \, \mu H/ft$

Insulation Resistance 100000 MOhms-km

Jacket Spark Test Voltage (rms) 6000 V

Operating Frequency Band 1 – 13000 MHz

Peak Power16.6 kWVelocity85 %

COMMSCOPE®

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
680-960 MHz	1.201	20.79
1700-2200 MHz	1.201	20.79
2200-2700 MHz	1.433	14.99

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.332	0.101	16.6
1.5	0.407	0.124	16.6
2.0	0.471	0.143	16.38
10.0	1.059	0.323	7.28
20.0	1.503	0.458	5.13
30.0	1.847	0.563	4.17
50.0	2.397	0.73	3.22
85.0	3.146	0.959	2.45
88.0	3.203	0.976	2.41
100.0	3.421	1.043	2.25
108.0	3.559	1.085	2.17
150.0	4.219	1.286	1.83
174.0	4.558	1.389	1.69
200.0	4.901	1.494	1.57
204.0	4.952	1.509	1.56
300.0	6.062	1.847	1.27
400.0	7.057	2.151	1.09
450.0	7.513	2.29	1.03
460.0	7.601	2.317	1.01
500.0	7.947	2.422	0.97
512.0	8.048	2.453	0.96
600.0	8.761	2.67	0.88
700.0	9.519	2.901	0.81
800.0	10.232	3.119	0.75
824.0	10.398	3.169	0.74
894.0	10.869	3.313	0.71

Page 2 of 5

960.0	11.299	3.444	0.68
1000.0	11.554	3.521	0.67
1218.0	12.874	3.924	0.6
1250.0	13.059	3.98	0.59
1500.0	14.446	4.403	0.53
1700.0	15.49	4.721	0.5
1794.0	15.964	4.866	0.48
1800.0	15.994	4.875	0.48
2000.0	16.97	5.172	0.45
2100.0	17.443	5.316	0.44
2200.0	17.908	5.458	0.43
2300.0	18.365	5.597	0.42
2500.0	19.257	5.869	0.4
2700.0	20.122	6.133	0.38
3000.0	21.376	6.515	0.36
3400.0	22.978	7.003	0.34
3600.0	23.754	7.24	0.32
3700.0	24.136	7.356	0.32
3800.0	24.514	7.471	0.31
3900.0	24.888	7.586	0.31
4000.0	25.26	7.699	0.31
4100.0	25.627	7.811	0.3
4200.0	25.992	7.922	0.3
4300.0	26.354	8.032	0.29
4400.0	26.713	8.142	0.29
4500.0	27.069	8.25	0.28
4600.0	27.422	8.358	0.28
4700.0	27.773	8.465	0.28
4800.0	28.12	8.571	0.27
4900.0	28.466	8.676	0.27
5000.0	28.809	8.781	0.27
6000.0	32.121	9.79	0.24
8000.0	38.244	11.656	0.2
8800.0	40.551	12.359	0.19
10000.0	43.894	13.378	0.18

12000.0 49.209 14.998 0.16

Material Specifications

Dielectric Material Foam PE

Jacket Material Non-halogenated, fire retardant polyolefin

Inner Conductor Material Copper-clad aluminum wire

Outer Conductor Material Corrugated copper

Mechanical Specifications

Minimum Bend Radius, multiple Bends95.25 mm3.75 inMinimum Bend Radius, single Bend40.64 mm1.6 in

Number of Bends, minimum 15 Number of Bends, typical 50

 Tensile Strength
 113 kg | 249.122 lb

 Bending Moment
 1.9 N-m | 16.816 in lb

 Flat Plate Crush Strength
 2 kg/mm | 111.995 lb/in

Environmental Specifications

Installation temperature $-40 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Attenuation, Ambient Temperature $68 \, ^{\circ}\text{F} \mid 20 \, ^{\circ}\text{C}$ Average Power, Ambient Temperature $104 \, ^{\circ}\text{F} \mid 40 \, ^{\circ}\text{C}$ Average Power, Inner Conductor Temperature $212 \, ^{\circ}\text{F} \mid 100 \, ^{\circ}\text{C}$

Fire Retardancy Test Method | IEC 60332-1 | IEC 60332-3C-24 | NFPA 130-2010 | UL 1666/CATVR

Smoke Index Test Method IEC 61034

Toxicity Index Test Method IEC 60754-1 | IEC 60754-2

Packaging and Weights

Cable weight 0.12 kg/m | 0.081 lb/ft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant



