

FOWB Fiber Optic Wall Box, 12 singlemode duplex LC/APC adapters only



## Product Classification

|                              |                |
|------------------------------|----------------|
| <b>Product Type</b>          | Fiber wall box |
| <b>Product Series</b>        | FOWB           |
| <b>Regional Availability</b> | EMEA           |

## General Specifications

|                                   |            |
|-----------------------------------|------------|
| <b>Adapters, quantity</b>         | 12         |
| <b>Color</b>                      | Light gray |
| <b>Interface Feature, input</b>   | APC        |
| <b>Interface, input</b>           | LC         |
| <b>Package, quantity</b>          | 1          |
| <b>Port, quantity</b>             | 24         |
| <b>Splicing Capacity, maximum</b> | 24         |

## Dimensions

|               |                     |
|---------------|---------------------|
| <b>Depth</b>  | 35.00 mm   1.38 in  |
| <b>Height</b> | 220.00 mm   8.66 in |
| <b>Width</b>  | 140.00 mm   5.51 in |

## Dimension Drawing

|                          |                              |
|--------------------------|------------------------------|
| <b>Dimension Drawing</b> | Used as an image placeholder |
|--------------------------|------------------------------|

## Mechanical Specifications

|                      |               |
|----------------------|---------------|
| <b>Material Type</b> | Thermoplastic |
| <b>Mount Type</b>    | Wall          |

## Optical Specifications

|                   |            |
|-------------------|------------|
| <b>Fiber Mode</b> | Singlemode |
|-------------------|------------|

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Environmental Space</b>   | Indoor                               |
| <b>Flammability Rating</b>   | UL 94 V-0                            |
| <b>Operating Temperature</b> | -25 °C to +70 °C (-13 °F to +158 °F) |

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant



## Included Products

CZ8468-000 | FOWB-T-NNNNN — FOWB Fiber Optic Wall Box, empty for holding up to 12 adapters

FOWB Fiber Optic Wall Box, empty for holding up to 12 adapters



## Product Classification

|                              |                |
|------------------------------|----------------|
| <b>Product Type</b>          | Fiber wall box |
| <b>Product Series</b>        | FOWB           |
| <b>Regional Availability</b> | EMEA           |

## General Specifications

|                                   |            |
|-----------------------------------|------------|
| <b>Adapters, quantity</b>         | 0          |
| <b>Color</b>                      | Light gray |
| <b>Package, quantity</b>          | 1          |
| <b>Splicing Capacity, maximum</b> | 24         |

## Dimensions

|               |                     |
|---------------|---------------------|
| <b>Depth</b>  | 35.00 mm   1.38 in  |
| <b>Height</b> | 220.00 mm   8.66 in |
| <b>Width</b>  | 140.00 mm   5.51 in |

## Dimension Drawing

|                          |                              |
|--------------------------|------------------------------|
| <b>Dimension Drawing</b> | Used as an image placeholder |
|--------------------------|------------------------------|

## Mechanical Specifications

|                      |               |
|----------------------|---------------|
| <b>Material Type</b> | Thermoplastic |
| <b>Mount Type</b>    | Wall          |

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Environmental Space</b>   | Indoor                               |
| <b>Flammability Rating</b>   | UL 94 V-0                            |
| <b>Operating Temperature</b> | -25 °C to +70 °C (-13 °F to +158 °F) |

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

