



IWB Fiber Wall Box, 2-door, singlemode FC/UPC, 12-ports, with pigtails and splice tray, 2 cable clamps

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

**OBSOLETE**

This product was discontinued on: March 1, 2018

### Product Classification

<b>Product Series</b>	IWB
<b>Product Type</b>	Fiber wall box
<b>Regional Availability</b>	Asia   EMEA

### Construction Materials

<b>Fiber Mode</b>	Singlemode
<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel
<b>Total Fibers, quantity</b>	12

### Dimensions

<b>Depth</b>	85.00 mm   3.35 in
<b>Height</b>	270.00 mm   10.63 in
<b>Width</b>	305.00 mm   12.01 in

### Environmental Specifications

<b>Environmental Space</b>	Indoor
<b>Qualification Standards</b>	NEMA type 12

### General Specifications

<b>Adapters, quantity</b>	12
<b>Application</b>	Patching   Splicing
<b>Cable Stub Type</b>	Pigtails, stranded
<b>Color</b>	Gray
<b>Door, quantity</b>	2
<b>Interface Feature, front</b>	Standard

<b>Interface, front</b>	FC
<b>Package Quantity</b>	1
<b>Packaging Type</b>	Bag   Carton
<b>Splice Trays Included, quantity</b>	0
<b>Splicing Capacity, maximum</b>	12
<b>Splicing Type</b>	Mass fusion
<b>Total Ports, quantity</b>	12

## Mechanical Specifications

<b>Cable Clamps, quantity</b>	2
<b>Cable Entry Location</b>	Bottom right   Top right
<b>Front Door Type</b>	Single hinged
<b>Mount Type</b>	Wall

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

