



FOSC™400 A4 Fiber Optic Splice Closure, Heat Shrink Cable sealing, two pre-installed 8-splice trays

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

### Product Classification

<b>Product Type</b>	Single-ended, round fiber closure
<b>Regional Availability</b>	Asia   EMEA
<b>Product Series</b>	FOSC 400
<b>Product Brand</b>	FOSC™


### General Specifications

<b>Splicing Type, Supported</b>	Single fusion
<b>Splicing Capacity, Single Fusion, maximum</b>	48
<b>Color</b>	Black
<b>Network Area Type</b>	Feeder
<b>Package, quantity</b>	1
<b>Packaging Type</b>	Box   Carton
<b>Splice Tray Included, quantity</b>	2
<b>Splice Tray Type Included</b>	8-way, heat shrink
<b>Splicing Capacity, Single Splice, 12 fibers, maximum</b>	48
<b>Splicing Capacity, Single Splice, 6 fibers, maximum</b>	24

### Dimensions

<b>Main Cable Diameter, maximum</b>	25.00 mm
<b>Diameter</b>	150.00 mm   5.91 in
<b>Diameter, with clamp</b>	180 mm   7 in
<b>Length</b>	420.00 mm   16.54 in
<b>Weight</b>	1.90 kg   4.19 lb

### Dimension Drawing



## Mechanical Specifications

<b>Cable Sealing Type</b>	Heat shrink
<b>Cable Entry Drop Port Style</b>	Round
<b>Cable Entry Main Port Style</b>	Oval
<b>Cable Ports, quantity</b>	5
<b>Closure Sealing Type</b>	Dome-to-base clamp with O-ring
<b>Closure Style</b>	Single-ended
<b>Material Type</b>	Impact-resistant polymer
<b>Mount Type</b>	Pole   Strand   Wall

## Environmental Specifications

<b>Environmental Space</b>	Below ground   Buried
<b>Qualification Standard</b>	IEC 61300, 6 m waterhead

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

