



HomeConnect® 75 Ohm XPRESSPREP® Coaxial Drop Cable with BrightWire® anti-corrosive treatment, Series 6, black flame retardant PVC jacket

## Product Classification

<b>Brand</b>	BrightWire®   HomeConnect®   XPRESSPREP®
<b>Product Type</b>	Coaxial drop cable
<b>Product Series</b>	6 Series

## Construction Materials

<b>Corrosion Protection</b>	BrightWire®
<b>Jacket Material</b>	Fire retardant PVC
<b>Center Conductor Material</b>	Copper-clad steel
<b>Dielectric Material</b>	Foam PE
<b>Inner Shield (Braid) Coverage</b>	77 %
<b>Inner Shield (Braid) Gauge</b>	34 AWG
<b>Inner Shield (Braid) Material</b>	Aluminum
<b>Inner Shield (Tape) Material</b>	Aluminum/Polymer/Aluminum (APA) bonded
<b>Outer Shield (Tape) Material</b>	Aluminum/Polymer/Aluminum (APA) bonded

## Dimensions

<b>Diameter Over Center Conductor, nominal</b>	1.016 mm   0.040 in
<b>Diameter Over Dielectric, nominal</b>	4.572 mm   0.180 in
<b>Diameter Over Inner Shield (Tape), nominal</b>	4.750 mm   0.187 in
<b>Diameter Over Jacket, nominal</b>	7.061 mm   0.278 in
<b>Jacket Thickness, nominal</b>	0.7620 mm   0.0300 in
<b>Shipping Weight</b>	34.00 lb/kft

## Electrical Specifications

<b>dc Resistance, Inner Conductor, nominal</b>	30.50 ohms/kft
<b>dc Resistance, Outer Conductor, nominal</b>	6.40 ohms/kft
<b>dc Resistance, Loop, nominal</b>	36.90 ohms/kft
<b>dc Resistance Note</b>	Nominal values based on a standard condition of 20 °C (68 °F)
<b>Capacitance</b>	53.1 pF/m   16.2 pF/ft
<b>Characteristic Impedance</b>	75 ohm
<b>Characteristic Impedance Tolerance</b>	±3 ohm
<b>Nominal Velocity of Propagation (NVP)</b>	85 %

## Environmental Specifications

**Environmental Space** Indoor  
**Flame Test Listing** CATV | CM | NEC Article 800 | NEC Article 820

## General Specifications

**Cable Type** Series 6  
**Packaging Type** Reel  
**Shield Construction Type** Trishield  
**Center Conductor Gauge** 18 AWG  
**Center Conductor Type** Solid  
**Jacket Color** Black  
**Jacket Marking** Feet  
**Warranty** One year

## Electrical Performance

Frequency	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5 MHz	1.90	0.58
55 MHz	5.25	1.60
83 MHz	6.40	1.95
85 MHz	6.46	1.97
187 MHz	9.35	2.85
204 MHz	9.84	3.00
211 MHz	10.00	3.05
250 MHz	10.82	3.30
300 MHz	11.64	3.55
350 MHz	12.63	3.85
400 MHz	13.61	4.15
450 MHz	14.43	4.40
500 MHz	15.29	4.66
550 MHz	16.08	4.90
600 MHz	16.73	5.10
750 MHz	18.54	5.65
865 MHz	20.01	6.10
1000 MHz	21.49	6.55
1218 MHz	23.66	7.21
1300 MHz	24.71	7.53
1400 MHz	25.71	7.84
1500 MHz	26.68	8.13
1600 MHz	27.63	8.42
1700 MHz	28.54	8.70
1794 MHz	29.39	8.96
1800 MHz	29.44	8.97
2000 MHz	31.17	9.50
2200 MHz	32.83	10.01
2500 MHz	35.20	10.73
2800 MHz	37.46	11.42
3000 MHz	38.91	11.86

*\* Attenuation listed represents maximum values at standard condition of 20 °C (68 °F)*

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

ISO 9001:2015

### Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

