

HomeConnect® 75 Ohm Coaxial Drop Cable, Series 50, black flame retardant PVC jacket



## Product Classification

<b>Brand</b>	HomeConnect®
<b>Product Type</b>	Coaxial drop cable
<b>Product Series</b>	50 Series

## Standards And Qualifications

<b>EN50575 CPR Cable EuroClass</b>	Dca   s2   d0
------------------------------------	---------------

## Construction Materials

<b>Jacket Material</b>	Fire retardant PVC
<b>Center Conductor Material</b>	Copper-clad aluminum
<b>Dielectric Material</b>	Foam PE
<b>Inner Shield (Braid) Coverage</b>	60 %
<b>Inner Shield (Braid) Gauge</b>	33 AWG
<b>Inner Shield (Braid) Material</b>	Aluminum
<b>Inner Shield (Tape) Material</b>	Aluminum/Polymer/Aluminum (APA) bonded
<b>Outer Shield (Tape) Material</b>	Aluminum/Polymer/Aluminum (APA)

## Dimensions

<b>Diameter Over Center Conductor, nominal</b>	2.769 mm   0.109 in
<b>Diameter Over Dielectric, nominal</b>	11.557 mm   0.455 in
<b>Diameter Over Inner Shield (Tape), nominal</b>	11.760 mm   0.463 in
<b>Diameter Over Jacket, nominal</b>	14.986 mm   0.590 in
<b>Jacket Thickness, nominal</b>	1.1938 mm   0.0470 in
<b>Shipping Weight</b>	108.00 lb/kft

## Electrical Specifications

<b>dc Resistance, Inner Conductor, nominal</b>	1.20 ohms/kft
<b>dc Resistance, Outer Conductor, nominal</b>	3.40 ohms/kft

<b>dc Resistance, Loop, nominal</b>	4.60 ohms/kft
<b>Operating Frequency Band</b>	5–3000 MHz
<b>dc Resistance Note</b>	Nominal values based on a standard condition of 20 °C (68 °F)
<b>Capacitance</b>	53.1 pF/m   16.2 pF/ft
<b>Characteristic Impedance</b>	75 ohm
<b>Characteristic Impedance Tolerance</b>	±3 ohm
<b>Nominal Velocity of Propagation (NVP)</b>	85 %

## Environmental Specifications

<b>Environmental Space</b>	Indoor
<b>Flame Test Listing</b>	CATV   CM   IEC 60332-1-2   NEC Article 800   NEC Article 820   UL 1685

## General Specifications

<b>Cable Type</b>	Series 50
<b>Packaging Type</b>	Reel
<b>Shield Construction Type</b>	Trishield
<b>Center Conductor Gauge</b>	9 AWG
<b>Center Conductor Type</b>	Solid
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Feet   Meters
<b>Warranty</b>	One year

## Electrical Performance

Frequency	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5 MHz	0.69	0.21
55 MHz	1.97	0.60
83 MHz	2.40	0.73
85 MHz	2.43	0.74
187 MHz	3.58	1.09
204 MHz	4.63	1.14
211 MHz	3.81	1.16
250 MHz	4.17	1.27
300 MHz	4.56	1.39
350 MHz	4.92	1.50
400 MHz	5.28	1.61
450 MHz	5.61	1.71
500 MHz	5.91	1.80
550 MHz	6.20	1.89
600 MHz	6.50	1.98
750 MHz	7.32	2.23
865 MHz	7.87	2.40
1000 MHz	8.50	2.59
1218 MHz	9.42	2.87
1300 MHz	9.81	2.99

1400 MHz	10.27	3.13
1500 MHz	10.70	3.26
1600 MHz	11.09	3.38
1700 MHz	11.52	3.51
1794 MHz	11.88	3.62
1800 MHz	11.91	3.63
2000 MHz	12.70	3.87
2200 MHz	13.45	4.10
2500 MHz	14.53	4.43
2800 MHz	15.59	4.75
3000 MHz	16.24	4.95

\* Attenuation listed represents maximum values at standard condition of 20 °C (68 °F)

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

ISO 9001:2015

CENELEC

### Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

EN 50575 compliant, Declaration of Performance (DoP) available

