

Fiber Indoor/Outdoor cable, Gel-Filled PBT Buffer Tube with 1 fiber, Singlemode G.657.A2/B2, 900um Tight-Buffered, 2.0 mm diameter, Feet jacket marking, White jacket color



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	A-20T


General Specifications

Fiber Type, quantity	1
Jacket Color	White
Jacket Marking	Feet
Subunit Type	Gel-filled
Total Fiber Count	1

Dimensions

Height Over Jacket	2 mm 0.079 in
---------------------------	-----------------

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded 50 mm | 1.969 in

Minimum Bend Radius, unloaded 30 mm | 1.181 in

Optical Specifications

Fiber Type G.657.A2/B2 | G.657.A2/B2

Environmental Specifications

Jacket UV Resistance Non UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Drip 80 °C | 176 °F

Drip Test Method FOTP-81

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



Included Products

CS-8G-TB – Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2)