

CNT-240-FR-600M

CNT-240-FR, CNT® 50 Ohm Braided Coaxial Cable, 600 m, black non-halogenated, fire retardant polyolefin jacket, Dca s2 d2 Compliant



OBSOLETE

Product Classification

Product Type	Braided coaxial cable
Product Brand	CNT®
Product Series	CNT-240

General Specifications

Braid Coverage	90 %
Cable Type	CNT-240
Jacket Color	Black

Dimensions

Cable Length	600 m 1,968.504 ft
Reel Flange	381 mm 15 in
Reel Hub	127 mm 5 in
Reel Traverse	305 mm 12.008 in
Diameter Over Dielectric	3.81 mm 0.15 in
Diameter Over Jacket	6.1 mm 0.24 in
Diameter Over Tape	3.987 mm 0.157 in
Inner Conductor OD	1.42 mm 0.056 in
Outer Conductor OD	4.52 mm 0.178 in
Nominal Size	0.240 in

Electrical Specifications

CNT-240-FR-600M

Cable Impedance	50 ohm
Capacitance	79.8 pF/m 24.323 pF/ft
dc Resistance, Inner Conductor	11.1 ohms/km 3.383 ohms/kft
dc Resistance, Outer Conductor	12.76 ohms/km 3.889 ohms/kft
dc Test Voltage	2500 V
Jacket Spark Test Voltage (rms)	2500 V
Maximum Frequency	31 GHz
Operating Frequency Band	30 – 6000 MHz
Peak Power	5.6 kW
Shielding Effectiveness	90 dB
Velocity	83 %

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
30.0	4.9	1.5
50.0	6.2	1.9
150.0	10.2	3.1
220.0	12.5	3.8
450.0	17.4	5.3
900.0	24.9	7.6
1800.0	35.75	10.9
2500.0	42.31	12.9
3000.0	46.48	14.17
4000.0	53.92	16.44
4500.0	57.3	17.47
5000.0	60.51	18.45
5200.0	61.76	18.83
5500.0	63.6	19.39
5800.0	66.9	20.4
6000.0	73.82	22.5

Material Specifications

Braid Material	Tinned copper
Dielectric Material	Foam PE

CNT-240-FR-600M

Jacket Material	Non-halogenated, fire retardant polyolefin
Inner Conductor Material	Copper
Shield Tape Material	Aluminum

Mechanical Specifications

Minimum Bend Radius, single Bend	19.05 mm 0.75 in
Tensile Strength	36 kg 79.366 lb
Bending Moment	0.3 N-m 2.655 in lb
Flat Plate Crush Strength	0.4 kg/mm 22.399 lb/in

Environmental Specifications

Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Storage Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
EN50575 CPR Cable EuroClass Fire Performance	Dca
EN50575 CPR Cable EuroClass Smoke Rating	s2
EN50575 CPR Cable EuroClass Droplets Rating	d2
Smoke Index Test Method	IEC 61034
Toxicity Index Test Method	IEC 60754-2

Packaging and Weights

Cable weight	0.05 kg/m 0.034 lb/ft
Packaging Type	Reel
Weight, gross	31.9 kg 70.327 lb

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

