# 5308203 | P3® 625 JCAM109



 \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

### **Product Classification**

Regional Availability North America

Product Type Coaxial hardline cable

Product Brand P3®

**Government Funding**Build America Buy America (BABA) compliant\*

**Warranty** One year

General Specifications

Cable Type625 SeriesConstruction TypeSwagedJacket ColorBlack

Short Description P3 625 JCAM109 SM PR2171

**Dimensions** 

Cable Length731.52 m | 2400 ftDiameter Over Center Conductor, nominal3.48 mm | 0.137 inDiameter Over Dielectric, nominal14.351 mm | 0.565 inDiameter Over Jacket, nominal17.399 mm | 0.685 inDiameter Over Outer Conductor, nominal15.875 mm | 0.625 inJacket Thickness, nominal0.762 mm | 0.03 inOuter Conductor Thickness, nominal0.762 mm | 0.03 in

**Electrical Specifications** 

**Capacitance** 50.197 pF/m | 15.3 pF/ft

**Capacitance Tolerance**  $\pm 1.0 \text{ pF/ft}$ 

COMMSCOPE®

# 5308203 | P3® 625 JCAM109

Characteristic Impedance75 ohmCharacteristic Impedance Tolerance±2 ohm

dc Resistance Note Nominal values based on a standard condition of 20 °C (68 °F)

dc Resistance, Inner Conductor, nominal2.756 ohms/km | 0.84 ohms/kftdc Resistance, Loop, nominal3.609 ohms/km | 1.1 ohms/kftdc Resistance, Outer Conductor, nominal0.853 ohms/km | 0.26 ohms/kft

Jacket Spark Test Voltage5000 VacNominal Velocity of Propagation (NVP)87 %

Operating Frequency Band 5-3000 MHz

**Structural Return Loss** 24 dB @ 1003-1218 MHz | 24 dB @ 1219-1794 MHz | 30 dB @ 5-1002

MHz

**Structural Return Loss, Grade N** ≥24 dB @ 1003−1218 MHz | ≥24 dB @ 1219−1794 MHz | ≥30 dB @ 5−1002

MHz

### Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.43	0.13
55.0	1.48	0.45
85.0	1.84	0.56
204.0	2.92	0.89
211.0	3.02	0.92
250.0	3.28	1
300.0	3.54	1.08
350.0	3.87	1.18
400.0	4.17	1.27
450.0	4.43	1.35
500.0	4.69	1.43
550.0	4.92	1.5
600.0	5.18	1.58
750.0	5.84	1.78
865.0	6.33	1.93
1002.0	6.92	2.11
1218.0	7.62	2.32
1500.0	8.74	2.66
1794.0	9.7	2.96





# 5308203 | P3® 625 JCAM109

1800.0	9.72	2.96
2000.0	10.34	3.15
2200.0	10.95	3.34
2500.0	11.81	3.6
2700.0	12.37	3.77
3000.0	13.19	4.02

### Material Specifications

Center Conductor Material Copper-clad aluminum

**Dielectric Material** Foam PE

Jacket Material PE

Outer Conductor Material Aluminum

Mechanical Specifications

Minimum Bend Radius, bonded114.3 mm4.5 inPulling Tension, maximum215.456 kg475 lb

### **Environmental Specifications**

Environmental Space Aerial

Packaging and Weights

Packaging Type Reel

**Weight, gross** 272.334 kg/km | 183 lb/kft

## Regulatory Compliance/Certifications

#### Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



