

WBC-400



WBC-400, 50 Ohm Braided Coaxial Cable, black PE jacket

OBSOLETE

This product was discontinued on: August 17, 2009

Replaced By:

CNT-400	CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket
CNT-400-100MKT	CNT-400, CNT® 50 Ohm Braided Coaxial Cable, 100 m, black PE jacket
CNT-400-150M	CNT-400, CNT® 50 Ohm Braided Coaxial Cable, 150 m, black PE jacket
CNT-400-300M	CNT-400, CNT® 50 Ohm Braided Coaxial Cable, 300 m, black PE jacket
CNT-400-500-RP	CNT-400, CNT® 50 Ohm Braided Coaxial Cable, 500 ft Reel-PAX, black PE jacket
CNT-400-500M	CNT-400, CNT® 50 Ohm Braided Coaxial Cable, 500 m, black PE jacket
CNT-400-503-AV	CNT-400, CNT® 50 Ohm Braided Coaxial Cable, 503 ft (+/- 6in), black PE jacket
CNT-400-50M	CNT-400, CNT® 50 Ohm Braided Coaxial Cable, 50 m, black PE jacket
CNT-400-75M	CNT-400, CNT® 50 Ohm Braided Coaxial Cable, 75 m, black PE jacket
CNT-400-E	CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket
CNT-400-LB	CNT-400, CNT® 50 Ohm Low Braided Coverage Coaxial Cable, variable, black PE jacket
CNT-400-SFR	CNT-400-SFR, C CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket, B2ca S1a d0 a1 Compliant
CNT-400-W	CNT-400-W, CNT® 50 Ohm Braided Coaxial Cable, variable, white PE jacket
CNT-400-WCP	CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket
CNT-400Q	CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket

Product Classification

Product Type	Braided coaxial cable
Product Brand	CNT®
Product Series	WBC-400

General Specifications

Braid Coverage	90 %
Cable Type	WBC-400
Jacket Color	Black

WBC-400

Dimensions

Diameter Over Dielectric	7.24 mm 0.285 in
Diameter Over Jacket	10.29 mm 0.405 in
Inner Conductor OD	2.74 mm 0.108 in
Outer Conductor OD	7.39 mm 0.291 in
Nominal Size	0.400 in

Electrical Specifications

Cable Impedance	50 ohm
Capacitance	78.4 pF/m 23.896 pF/ft
dc Resistance, Inner Conductor	4.33 ohms/km 1.32 ohms/kft
dc Resistance, Outer Conductor	6.89 ohms/km 2.1 ohms/kft
dc Test Voltage	2500 V
Jacket Spark Test Voltage (rms)	4000 V
Maximum Frequency	16.2 GHz
Operating Frequency Band	30 – 6000 MHz
Peak Power	16 kW
Velocity	85 %

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
30.0	2.3	0.7
50.0	2.95	0.9
150.0	4.92	1.5
220.0	6.23	1.9
450.0	8.86	2.7
900.0	12.79	3.9
1500.0	16.73	5.1
1800.0	18.7	5.7
2000.0	19.68	6
2500.0	22.3	6.8

Material Specifications

Braid Material	Tinned copper
-----------------------	---------------

WBC-400

Dielectric Material	Foam PE
Jacket Material	PE
Inner Conductor Material	Copper-clad aluminum wire
Shield Tape Material	Aluminum

Mechanical Specifications

Minimum Bend Radius, single Bend	50.038 mm 1.97 in
Tensile Strength	73 kg 160.937 lb

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

Packaging and Weights

Cable weight	0.1 kg/m 0.067 lb/ft
Packaging Type	Reel