5518102 | QR® 715 JCASS

75 Ohm QR® Trunk and Distribution Cable, black PE jacket, flooded for underground



*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability North America

Product Type Coaxial hardline cable

Product Brand QR®

Government FundingBuild America Buy America (BABA) compliant*

General Specifications

Cable Type715 SeriesConstruction TypeWeldedJacket ColorBlack

Short Description QR 715 JCASS SM PR997

Dimensions

Cable Length914.4 m | 3000 ftDiameter Over Center Conductor, nominal4.216 mm | 0.166 inDiameter Over Dielectric, nominal17.424 mm | 0.686 inDiameter Over Jacket, nominal19.939 mm | 0.785 inDiameter Over Outer Conductor, nominal18.161 mm | 0.715 inJacket Thickness, nominal0.889 mm | 0.035 inOuter Conductor Thickness, nominal0.368 mm | 0.014 in

Electrical Specifications

Capacitance 50.197 pF/m | 15.3 pF/ft

Capacitance Tolerance±1.0 pF/ftCharacteristic Impedance75 ohm



5518102 | QR® 715 JCASS

Characteristic Impedance Tolerance ±2 ohm

dc Resistance Note

Nominal values based on a standard condition of 20 °C (68 °F)

dc Resistance, Inner Conductor, nominal 1.903 ohms/km | 0.58 ohms/kft

dc Resistance, Loop, nominal 3.281 ohms/km | 1 ohms/kft

dc Resistance, Outer Conductor, nominal 1.378 ohms/km | 0.42 ohms/kft

Jacket Spark Test Voltage 5000 Vac

Nominal Velocity of Propagation (NVP) 88 %

Operating Frequency Band 5-3000 MHz

Structural Return Loss 24 dB @ 1003-1218 MHz | 24 dB @ 1219-1794 MHz | 30 dB @ 5-1002

MHz

Structural Return Loss, Grade N ≥24 dB @ 1003−1218 MHz | ≥24 dB @ 1219−1794 MHz | ≥30 dB @ 5−1002

ИHz

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.36	0.11
55.0	1.21	0.37
85.0	1.51	0.46
204.0	2.4	0.73
211.0	2.43	0.74
250.0	2.66	0.81
300.0	2.92	0.89
350.0	3.18	0.97
400.0	3.44	1.05
450.0	3.67	1.12
500.0	3.9	1.19
550.0	4.1	1.25
600.0	4.3	1.31
750.0	4.89	1.49
865.0	5.31	1.62
1002.0	5.76	1.75
1218.0	6.43	1.96
1500.0	7.44	2.27
1794.0	8.3	2.53
1800.0	8.32	2.54



5518102 | QR® 715 JCASS

2000.0	8.88	2.71
2200.0	9.42	2.87
2500.0	10.21	3.11
2700.0	10.72	3.27
3000.0	11.46	3.49

Material Specifications

Center Conductor Material Copper-clad aluminum

Dielectric MaterialFoam PEJacket MaterialPE

Outer Conductor Material Aluminum

Mechanical Specifications

Minimum Bend Radius, bonded 127 mm | 5 in

Pulling Tension, maximum 154.221 kg | 340 lb

Environmental Specifications

 Corrosion Protection
 Migraheal®

 Environmental Space
 Buried

Packaging and Weights

Packaging Type Reel

Weight, gross 305.074 kg/km | 205 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



