

5530002 | QR® 715 JCAM188

75 Ohm QR® Trunk and Distribution Cable, black PE jacket with integrated figure 8 self-supporting galvanized stranded steel messenger



OBSOLETE

Product Classification

Product Type	Coaxial hardline cable
Product Brand	QR®

General Specifications

Cable Type	715 Series
Construction Type	Welded
Jacket Color	Black
Messenger Wire Type	Stranded
Short Description	QR 715 JCAM188 SM PR2171

Dimensions

Cable Length	914.4 m 3000 ft
Diameter Over Center Conductor, nominal	4.216 mm 0.166 in
Diameter Over Dielectric, nominal	17.424 mm 0.686 in
Diameter Over Jacket, nominal	19.939 mm 0.785 in
Diameter Over Messenger Wire, nominal	4.775 mm 0.188 in
Diameter Over Outer Conductor, nominal	18.161 mm 0.715 in
Jacket Thickness, nominal	0.889 mm 0.035 in
Outer Conductor Thickness, nominal	0.368 mm 0.014 in

Electrical Specifications

Capacitance	50.197 pF/m 15.3 pF/ft
--------------------	--------------------------

5530002 | QR® 715 JCAM188

Capacitance Tolerance	±1.0 pF/ft
Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±2 ohm
dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)
dc Resistance, Inner Conductor, nominal	1.903 ohms/km 0.58 ohms/kft
dc Resistance, Loop, nominal	3.281 ohms/km 1 ohms/kft
dc Resistance, Outer Conductor, nominal	1.378 ohms/km 0.42 ohms/kft
Jacket Spark Test Voltage	5000 Vac
Nominal Velocity of Propagation (NVP)	88 %
Operating Frequency Band	5–3000 MHz
Structural Return Loss	24 dB @ 1003–1218 MHz 24 dB @ 1219–1794 MHz 30 dB @ 5–1002 MHz
Structural Return Loss, Grade N	≥24 dB @ 1003–1218 MHz ≥24 dB @ 1219–1794 MHz ≥30 dB @ 5–1002 MHz

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.36	0.11
55.0	1.21	0.37
85.0	1.51	0.46
204.0	2.4	0.73
211.0	2.43	0.74
250.0	2.66	0.81
300.0	2.92	0.89
350.0	3.18	0.97
400.0	3.44	1.05
450.0	3.67	1.12
500.0	3.9	1.19
550.0	4.1	1.25
600.0	4.3	1.31
750.0	4.89	1.49
865.0	5.31	1.62
1002.0	5.76	1.75
1218.0	6.43	1.96
1500.0	7.44	2.27

5530002 | QR® 715 JCAM188

1794.0	8.3	2.53
1800.0	8.32	2.54
2000.0	8.88	2.71
2200.0	9.42	2.87
2500.0	10.21	3.11
2700.0	10.72	3.27
3000.0	11.46	3.49

Material Specifications

Center Conductor Material	Copper-clad aluminum
Dielectric Material	Foam PE
Jacket Material	PE
Messenger Wire Material	Steel
Outer Conductor Material	Aluminum

Mechanical Specifications

Minimum Bend Radius, bonded	127 mm 5 in
Messenger Wire Breaking Strength, minimum	1,769.01 kg 3900 lb
Pulling Tension, maximum	154.221 kg 340 lb

Environmental Specifications

Environmental Space	Aerial
----------------------------	--------

Packaging and Weights

Packaging Type	Reel
Weight, gross	447.937 kg/km 301 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

