


E#O® Coaxial/Fiber Hybrid Buried Cable



- E#O is a solution that enables service providers the ability to bridge HFC networks to FTTx. The E#O composite coaxial/fiber product line combines fiber, microducts, and coaxial cable under one jacket
- Serves businesses in a new commercial serving area
- Mitigates future cost of fiber installation
- Saves on initial installation due to “single sheath” vs. multiple sheaths
- Ideal for commercial data customers that also require video
- All products tested to industry standards
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or are the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

OBSOLETE

Product Classification

Product Type	Hybrid cable, coax and fiber
Product Brand	E#O®

General Specifications

Cable Series	P3 625
Total Fiber Count	24

Dimensions

Height	26.797 mm 1.055 in
Width	19.177 mm 0.755 in
Outer Jacket Thickness, nominal	0.762 mm 0.03 in

Material Specifications

Outer Jacket Material	Medium density polyethylene (MDPE)
------------------------------	------------------------------------

Mechanical Specifications

Minimum Bend Radius	114.3 mm 4.5 in
Pulling Tension, maximum	33.112 kg 73 lb

Environmental Specifications

Environmental Space Buried

Packaging and Weights

Weight, gross 373.529 kg/km | 251 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

