

AVA5-50FX, HELIAX® Andrew Virtual Air™ Coaxial Cable, corrugated copper, 7/8 in, black PE jacket (Halogen free jacketing non-fire-retardant)

CommScope® non-standard product | Not available in the United States or

Coaxial wireless cable

520096403/00 | SZ520096403/00

Attenuation values typical, guaranteed within 5%

HELIAX®

Canada

Standard

24.13 mm | 0.95 in 27.991 mm | 1.102 in 9.449 mm | 0.372 in

25.4 mm | 1 in

7/8 in

Black

AVA5-50FX

Product Classification

Product Type Product Brand

Product Series

Ordering Note

General Specifications

Product Number Flexibility Jacket Color Performance Note

Dimensions

Diameter Over Dielectric
Diameter Over Jacket
Inner Conductor OD
Outer Conductor OD
Nominal Size

Electrical Specifications

Cable Impedance	50 ohm ±1 ohm
Capacitance	73 pF/m 22.25 pF/ft
dc Resistance, Inner Conductor	2.888 ohms/km 0.88 ohms/kft
dc Resistance, Outer Conductor	1.53 ohms/km 0.466 ohms/kft
dc Test Voltage	6000 V

Page 1 of 5



Inductance	0.184 µH/m 0.056 µH/ft
Insulation Resistance	100000 MOhms-km
Jacket Spark Test Voltage (rms)	8000 V
Operating Frequency Band	1 – 5000 MHz
Peak Power	91 kW
Velocity	90 %

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
680-800 MHz	1.13	24.3
800–960 MHz	1.13	24.3
1700–2200 MHz	1.13	24.3

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.113	0.034	74.43
1.5	0.138	0.042	60.73
2.0	0.16	0.049	52.56
10.0	0.359	0.11	23.37
20.0	0.51	0.156	16.46
30.0	0.627	0.191	13.39
50.0	0.814	0.248	10.32
85.0	1.068	0.326	7.86
88.0	1.088	0.332	7.72
100.0	1.162	0.354	7.23
108.0	1.209	0.368	6.95
150.0	1.433	0.437	5.86
174.0	1.548	0.472	5.43
200.0	1.665	0.507	5.05
204.0	1.682	0.513	4.99
300.0	2.059	0.628	4.08
400.0	2.398	0.731	3.5
450.0	2.553	0.778	3.29
460.0	2.583	0.787	3.25
500.0	2.7	0.823	3.11

Page 2 of 5



512.0	2.735	0.834	3.07
600.0	2.977	0.907	2.82
700.0	3.235	0.986	2.6
800.0	3.478	1.06	2.42
824.0	3.534	1.077	2.38
894.0	3.694	1.126	2.27
960.0	3.841	1.171	2.19
1000.0	3.927	1.197	2.14
1218.0	4.377	1.334	1.92
1250.0	4.44	1.353	1.89
1500.0	4.912	1.497	1.71
1700.0	5.268	1.605	1.59
1794.0	5.429	1.655	1.55
1800.0	5.439	1.658	1.54
2000.0	5.771	1.759	1.46
2100.0	5.933	1.808	1.42
2200.0	6.091	1.856	1.38
2300.0	6.247	1.904	1.34
2500.0	6.55	1.996	1.28
2700.0	6.845	2.086	1.23
3000.0	7.272	2.217	1.15
3400.0	7.819	2.383	1.07
3600.0	8.083	2.464	1.04
3700.0	8.213	2.503	1.02
3800.0	8.342	2.542	1.01
3900.0	8.47	2.581	0.99
4000.0	8.596	2.62	0.98
4100.0	8.722	2.658	0.96
4200.0	8.846	2.696	0.95
4300.0	8.969	2.734	0.94
4400.0	9.092	2.771	0.92
4500.0	9.213	2.808	0.91
4600.0	9.333	2.845	0.9
4700.0	9.453	2.881	0.89
4800.0	9.572	2.917	0.88

Page 3 of 5



4900.0	9.689	2.953	0.87	
5000.0	9.806	2.989	0.86	
Material Specification	วทร			
Dielectric Material		Foam PE		
Jacket Material		PE		
Inner Conductor Material		Copper		
Outer Conductor Material		Corrugated copper		
Mechanical Specific	ations			
Minimum Bend Radius, multip	ole Bends	254 mm 10 in		
Minimum Bend Radius, single	Bend	127 mm 5 in		
Number of Bends, minimum		15		
Number of Bends, typical		30		
Tensile Strength		159 kg 350.535 lb		
Bending Moment		19 N-m 168.164 in lb		
Flat Plate Crush Strength		1.3 kg/mm 72.797 lb/in		

Environmental Specifications

Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-55 °C to +70 °C (-67 °F to +158 °F)
Storage Temperature	-70 °C to +70 °C (-94 °F to +158 °F)
Attenuation, Ambient Temperature	68 °F 20 °C
Average Power, Ambient Temperature	104 °F 40 °C
Average Power, Inner Conductor Temperature	212 °F 100 °C

Packaging and Weights

Cable weight

0.41 kg/m | 0.276 lb/ft

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 4 of 5



ROHS UK-ROHS Compliant

Compliant



Page 5 of 5

