CK0475-000 | IFDB-M-SP-U-NN-1



IFDB Fiber Optic Wall Box with Universal splice holder for up to 12 mechanical or SMOUV splices

- Allows splicing those fibers from an indoor riser cable to the individual drops
- · Allows fibers from certain riser cables to be broken out without interrupting the strength member
- Separate storage of un-connected fibers from spliced drop fibers
- Compatible with mechanical, SMOUV and ANT splice protectors
- In-line and butt configuration possible for main riser cable

Product Classification

Regional Availability EMEA

Product Type Fiber wall box

Product Series IFDB

General Specifications

Functionality Splicing

Adapters, quantity 0

ColorLight grayFront Cover TypeScrew-onInterfaceSplicing onlyMountingFloor | Wall

Splice Tray Chip Type Mechanical | SMOUV

Splicing Capacity, maximum 12

Dimensions

 Height
 200 mm | 7.874 in


 Width
 126 mm | 4.961 in

 Depth
 50 mm | 1.969 in

Outline Drawing



CKO475-000 | IFDB-M-SP-U-NN-1



Material Specifications

Material Type Thermoplastic

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor **Flammability Rating** UL 94 V-0

Qualification Standards IEC 60529, IP30

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



COMMSC PE°

CKO475-000 | IFDB-M-SP-U-NN-1

