# CK6000-000 | IFDB-S-U-NN-1



# IFDB Fiber Optic Wall Box with Universal splice holder for up to 4 mechanical or SMOUV splices

- Allows splicing those fibers from an indoor riser cable to the individual drops
- Allows fibers from certain riser cables to be broken out without interrupting the strength member
- Separate storage of un-connected fibers from spliced drop fibers
- Compatible with mechanical, SMOUV and ANT splice protectors
- In-line and butt configuration possible for main riser cable

### Product Classification

Regional Availability	EMEA
Product Type	Fiber wall box
Product Series	IFDB

# General Specifications

Functionality	Splicing
Adapters, quantity	0
Color	Light gray
Front Cover Type	Screw-on
Interface	Splicing only
Mounting	Floor   Wall
Splice Tray Chip Type	Mechanical   SMOUV
Splicing Capacity, maximum	4

## Dimensions

Height	80 mm	3.15 in
Width	80 mm	3.15 in
Depth	35 mm	1.378 in

## Material Specifications

Thermoplastic

# Optical Specifications

#### Fiber Mode

Material Type

Singlemode

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 5, 2023



# CK6000-000 | IFDB-S-U-NN-1

### **Environmental Specifications**

Environmental Space	Indoor
Flammability Rating	UL 94 V-0
Qualification Standards	IEC 60529, IP30

### Packaging and Weights

Packaging quantity	20		
Packaging Type	Bag		Carton

# Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant





©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 5, 2023

