

760093377 | 360-iP-HD-MOD-LC-TS-3



SYSTIMAX 360™ iPatch® G2 Singlemode High Density Module, 3 pack

OBSOLETE

This product was discontinued on: October 20, 2022

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	SYSTIMAX 360™ iPatch®

General Specifications

Functionality	Breakout
Adapters, quantity, rear	12
Color, front	Blue
Color, housing	Black
Color, rear	Black
Intelligence Type	iPatch® enabled
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Reduced footprint
Total Ports, quantity, front	144

Dimensions

Height	82.55 mm 3.25 in
Width	152.4 mm 6 in
Depth	215.9 mm 8.5 in

Material Specifications

760093377 | 360-iP-HD-MOD-LC-TS-3

Material Type Acrylonitrile butadiene styrene (ABS) | Polycarbonate (PC)

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2

Insertion Loss Change, mating 0.3 dB

Insertion Loss Change, temperature 0.3 dB

Insertion Loss, maximum 1.05 dB

Environmental Specifications

Operating Temperature -5 °C to +50 °C (+23 °F to +122 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard ACMA | CE | CSA | UL

Packaging and Weights

Packaging quantity 3

Weight, net 1.13 kg | 2.491 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Insertion Loss Change, mating Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)