

# 999903070 | 3010B SLT C3 100/24 U/UTP RL 1000M



3010B Category 3 U/UTP Cable, low smoke zero halogen, slate jacket, 100 pair count, 1,000 m length reel

## OBSOLETE

This product was discontinued on: August 31, 2022

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America

### Portfolio

CommScope®

### Product Type

Twisted pair cable

## General Specifications

### Product Number

3010B

### ANSI/TIA Category

3

### Cable Component Type

Backbone

### Cable Type

U/UTP (unshielded)

### Conductor Type, singles

Solid

### Conductors, quantity

200

### Jacket Color

Slate

### Pairs, quantity

100

### Transmission Standards

ANSI/TIA-568.2-D

## Dimensions

### Cable Length

1,000 m | 3,280.84 ft

### Diameter Over Jacket, nominal

26.899 mm | 1.059 in

### Jacket Thickness

0.787 mm | 0.031 in

### Conductor Gauge, singles

24 AWG

# 999903070 | 3010B SLT C3 100/24 U/UTP RL 1000M

---

## Electrical Specifications

<b>Characteristic Impedance</b>	100 ohm
<b>Characteristic Impedance Tolerance</b>	±15 ohm
<b>dc Resistance Unbalance, maximum</b>	5 %
<b>dc Resistance, maximum</b>	9.38 ohms/100 m   2.859 ohms/100 ft
<b>Mutual Capacitance at Frequency</b>	6.6 nF/100 m @ 1 kHz
<b>Operating Frequency, maximum</b>	16 MHz
<b>Operating Voltage, maximum</b>	80 V

## Material Specifications

<b>Conductor Material</b>	Bare copper
<b>Insulation Material</b>	Polyolefin
<b>Jacket Material</b>	Low Smoke Zero Halogen (LSZH)

## Environmental Specifications

<b>Installation temperature</b>	-10 °C to +50 °C (+14 °F to +122 °F)
<b>Operating Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Acid Gas Test Method</b>	IEC 60754-2
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	Eca
<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
<b>Flame Test Method</b>	IEC 60332-3-22
<b>Smoke Test Method</b>	IEC 61034-2

## Packaging and Weights

<b>Cable weight</b>	742.996 kg/km   499.27 lb/kft
<b>Packaging Type</b>	Reel

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

