

E201177TSEF XP - 24 CT MICFIBR

E20® Coaxial/Fiber Hybrid Buried Cable



- E20 is a solution that enables service providers the ability to bridge HFC networks to FTTx. The E20 composite coaxial/fiber product line combines fiber, microducts, and coaxial cable under one jacket
- Serves businesses in a new commercial serving area
- Mitigates future cost of fiber installation
- Saves on initial installation due to “single sheath” vs. multiple sheaths
- Ideal for commercial data customers that also require video
- All products tested to industry standards

OBSOLETE

Product Classification

Product Type	Hybrid cable, coax and fiber
Product Brand	E20®
Product Series	11 Series

General Specifications

Cable Series	Series 11
Total Fiber Count	24

Dimensions

Height	17.272 mm 0.68 in
Width	11.684 mm 0.46 in
Outer Jacket Thickness, nominal	0.762 mm 0.03 in

Material Specifications

Outer Jacket Material	Medium density polyethylene (MDPE)
------------------------------	------------------------------------

Mechanical Specifications

Minimum Bend Radius	81.28 mm 3.2 in
Pulling Tension, maximum	33.112 kg 73 lb

Environmental Specifications

E201177TSEF XP - 24 CT MICFIBR

Environmental Space

Buried

Packaging and Weights

Weight, gross

119.053 kg/km | 80 lb/kft

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



Included Products

- 4846203
F1177TSEF XP – XPRESSPREP® Coaxial Drop Cable, 75 Ohm, Series 11, black PE jacket, flooded for underground
- 810008925/DB
B-024-LN-8W-F12NS/16G – LightScope ZWP® Blown Micro Single Jacket All-Dielectric Outdoor Stranded Loose Tube Arid-Core® Construction Cable