

# E20540JCASS-16MB DUCT

## E20® Coaxial/Microduct Hybrid Buried Cable



- E20 is a solution that enables service providers the ability to bridge HFC networks to FTTx. The E20 composite coaxial/fiber product line combines fiber, microducts, and coaxial cable under one jacket
- Serves businesses in a new commercial serving area
- Mitigates future cost of fiber installation
- Saves on initial installation due to “single sheath” vs. multiple sheaths
- Ideal for commercial data customers that also require video
- All products tested to industry standards

**OBSOLETE**

### Product Classification

<b>Product Type</b>	Hybrid cable, coax and fiber-duct
<b>Product Brand</b>	E20®

### General Specifications

<b>Cable Series</b>	QR 540
---------------------	--------

### Dimensions

<b>Height</b>	32.893 mm   1.295 in
<b>Width</b>	17.018 mm   0.67 in
<b>Outer Jacket Thickness, nominal</b>	0.762 mm   0.03 in

### Material Specifications

<b>Outer Jacket Material</b>	Medium density polyethylene (MDPE)
------------------------------	------------------------------------

### Mechanical Specifications

<b>Minimum Bend Radius</b>	203.2 mm   8 in
<b>Pulling Tension, maximum</b>	95.254 kg   210 lb

### Environmental Specifications

<b>Environmental Space</b>	Buried
----------------------------	--------

# E20540JCASS-16MB DUCT

---

## Packaging and Weights

**Weight, gross** 276.798 kg/km | 186 lb/kft

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system



## Included Products

5510192  
QR® 540 JCASS – 75 Ohm QR® Trunk and Distribution Cable, black PE jacket, flooded for underground

# 5510192 | QR® 540 JCASS

75 Ohm QR® Trunk and Distribution Cable, black PE jacket, flooded for underground



## Product Classification

<b>Product Type</b>	Coaxial hardline cable
<b>Product Brand</b>	QR®

## General Specifications

<b>Cable Type</b>	540 Series
<b>Construction Type</b>	Welded
<b>Jacket Color</b>	Black
<b>Short Description</b>	QR 540 JCASS SM PR2171

## Dimensions

<b>Cable Length</b>	1,127.76 m   3700 ft
<b>Diameter Over Center Conductor, nominal</b>	3.15 mm   0.124 in
<b>Diameter Over Dielectric, nominal</b>	13.056 mm   0.514 in
<b>Diameter Over Jacket, nominal</b>	15.494 mm   0.61 in
<b>Diameter Over Outer Conductor, nominal</b>	13.716 mm   0.54 in
<b>Jacket Thickness, nominal</b>	0.889 mm   0.035 in
<b>Outer Conductor Thickness, nominal</b>	0.343 mm   0.014 in

## Electrical Specifications

<b>Capacitance</b>	50.197 pF/m   15.3 pF/ft
<b>Capacitance Tolerance</b>	±1.0 pF/ft
<b>Characteristic Impedance</b>	75 ohm
<b>Characteristic Impedance Tolerance</b>	±2 ohm
<b>dc Resistance Note</b>	Nominal values based on a standard condition of 20 °C (68 °F)

# 5510192 | QR® 540 JCASS

<b>dc Resistance, Inner Conductor, nominal</b>	3.346 ohms/km   1.02 ohms/kft
<b>dc Resistance, Loop, nominal</b>	5.282 ohms/km   1.61 ohms/kft
<b>dc Resistance, Outer Conductor, nominal</b>	1.936 ohms/km   0.59 ohms/kft
<b>Jacket Spark Test Voltage</b>	5000 Vac
<b>Nominal Velocity of Propagation (NVP)</b>	88 %
<b>Operating Frequency Band</b>	5–3000 MHz
<b>Structural Return Loss</b>	24 dB @ 1003–1218 MHz   24 dB @ 1219–1794 MHz   30 dB @ 5–1002 MHz
<b>Structural Return Loss, Grade N</b>	=24 dB @ 1003–1218 MHz   =24 dB @ 1219–1794 MHz   =30 dB @ 5–1002 MHz

## Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.46	0.14
55.0	1.54	0.47
85.0	1.94	0.59
204.0	3.05	0.93
211.0	3.12	0.95
250.0	3.38	1.03
300.0	3.71	1.13
350.0	4.04	1.23
400.0	4.33	1.32
450.0	4.59	1.4
500.0	4.89	1.49
550.0	5.12	1.56
600.0	5.38	1.64
750.0	6.07	1.85
865.0	6.56	2
1002.0	7.12	2.17
1218.0	7.89	2.41
1500.0	9.07	2.76
1794.0	10.11	3.08
1800.0	10.13	3.09
2000.0	10.81	3.29
2200.0	11.46	3.49

# 5510192 | QR® 540 JCASS

---

<b>2500.0</b>	12.41	3.78
<b>2700.0</b>	13.03	3.97
<b>3000.0</b>	13.93	4.24

## Material Specifications

<b>Center Conductor Material</b>	Copper-clad aluminum
<b>Dielectric Material</b>	Foam PE
<b>Jacket Material</b>	PE
<b>Outer Conductor Material</b>	Aluminum

## Mechanical Specifications

<b>Pulling Tension, maximum</b>	99.79 kg   220 lb
---------------------------------	-------------------

## Environmental Specifications

<b>Corrosion Protection</b>	Migraheal®
<b>Environmental Space</b>	Buried

## Packaging and Weights

<b>Packaging Type</b>	Reel
<b>Weight, gross</b>	178.58 kg/km   120 lb/kft

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

