

# E20677TSEF XP - 6 CT MICFIBR

## E20® Coaxial/Fiber Hybrid Buried Cable



- E20 is a solution that enables service providers the ability to bridge HFC networks to FTTx. The E20 composite coaxial/fiber product line combines fiber, microducts, and coaxial cable under one jacket
- Serves businesses in a new commercial serving area
- Mitigates future cost of fiber installation
- Saves on initial installation due to “single sheath” vs. multiple sheaths
- Ideal for commercial data customers that also require video
- All products tested to industry standards

**OBSOLETE**

### Product Classification

<b>Product Type</b>	Hybrid cable, coax and fiber
<b>Product Brand</b>	E20®
<b>Product Series</b>	6 Series

### General Specifications

<b>Cable Series</b>	Series 6
<b>Total Fiber Count</b>	6

### Dimensions

<b>Height</b>	14.173 mm   0.558 in
<b>Width</b>	8.585 mm   0.338 in
<b>Outer Jacket Thickness, nominal</b>	0.762 mm   0.03 in

### Material Specifications

<b>Outer Jacket Material</b>	Medium density polyethylene (MDPE)
------------------------------	------------------------------------

### Mechanical Specifications

<b>Minimum Bend Radius</b>	81.28 mm   3.2 in
<b>Pulling Tension, maximum</b>	33.112 kg   73 lb

### Environmental Specifications

# E20677TSEF XP - 6 CT MICFIBR

---

**Environmental Space**

Buried

Packaging and Weights

**Weight, gross**

93.754 kg/km | 63 lb/kft

Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

