

300100110040 | NGFB-TB5SLUK0KP050



Next Generation Frame (NGF) Fiber Termination Block with Trunk Cable, LSZH rated, singlemode, OS2, 288 LC/UPC to Stub tail, left oriented, upward cable exit, black, 50 m

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Fiber patch block, with IFC cable
Product Series	NGFB

General Specifications

Functionality	Patching
Application	Used in NGF-style frames only
Body Style	Left orientation
Cable Exit Location	Upward
Cable Type	IFC - Stranded
Color	Black
Color, front	Black
Door Type, front	Compression latch Hinged
Growth Configuration	Fully loaded
Interface, front	LC/UPC
Interface, rear	Stub tail
Rack Type	NGF
Shelf Movement	Fixed
Total Ports, quantity	288

Dimensions

Cable Length	50
---------------------	----

Material Specifications

300100110040 | NGFB-TB5SLUKOKP050

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Fiber Type OS2

Environmental Specifications

Operating Temperature -5 °C to +50 °C (+23 °F to +122 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 80%, non-condensing

Qualification Standards Telcordia GR-449-CORE

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

