

# FEC-18-RM



## Fiber Optic Entrance Cabinet, 18 Drawers, Rack mounted

- Provides splicing, administration and storage for outside plant (OSP) and intrafacility cables (IFC)
- Offers a cost-effective, space-saving alternative to splicing on the fiber frame
- Cabinets are designed for deployment in a building equipment area
- Bend radius protection and discrete subunit routing paths ensure easy installation
- Can deploy high count of stranded or ribbon fiber cables
- Ultra high density splice capacity dependent on splice tray used

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Product Type</b>	Fiber entrance cabinet
<b>Product Series</b>	FEC

## General Specifications

<b>Access</b>	Front   Rear
<b>Cable Entry Location</b>	Bottom   Side   Top
<b>Cable Exit Location</b>	Bottom   Side   Top
<b>Color</b>	Putty white
<b>Mounting</b>	Rack, EIA 23 in
<b>Splice Drawers, quantity</b>	18
<b>Splice Trays Included, quantity</b>	0
<b>Splicing Capacity Note</b>	18 times number of splices per tray (example 18x288 = 5184)

## Dimensions

<b>Height</b>	914.4 mm   36 in
<b>Width</b>	660.4 mm   26 in
<b>Depth</b>	381 mm   15 in

## Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

## Packaging and Weights

<b>Included</b>	Grommets
-----------------	----------

# FEC-18-RM

---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted

