## FDT-CJ048NXR6000



iFDT Indoor Fiber Distribution Terminal, 48-fiber, SC/APC, ribbon IFC cable, 6000 feet

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

#### **Product Classification**

Regional Availability North America

**Product Type** Fiber distribution terminal

Product Series IFDT

### General Specifications

Adapters, quantity 48

 Cable Entry Location
 Bottom right | Top right

Cable TypeIFC - RibbonColorPutty whiteFront Door TypeDouble hinged

Growth Configuration Fully loaded Interface SC/APC

Interface, stubNo connectorLock TypePadlock ready

Mounting Wall
Port, quantity 48

#### **Dimensions**

 Height
 476.25 mm | 18.75 in

 Width
 368.3 mm | 14.5 in


 Depth
 127 mm | 5 in

**Cable Length** 1,828.8 m | 6000 ft

Ordering Tree

COMMSC PE°

# FDT-CJ048NXR6000



#### Material Specifications

**Finish** Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

## **Environmental Specifications**

Environmental Space Indoor

**Qualification Standards** NEMA, Type 12 | Telcordia GR-2898-CORE

Packaging and Weights

Packaging quantity 1



# FDT-CJ048NXR6000

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

