

# 760193805 | 360-iP-INSTA-LC-4LS



## SYSTIMAX 360™ iPatch® G2 Fiber Panel with InstaPATCH 360 LazrSPEED Modules

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber splice panel
<b>Product Brand</b>	SYSTIMAX 360™   iPatch®

### General Specifications

<b>Color</b>	Black
<b>Intelligence Type</b>	iPatch® enabled
<b>Interface, front</b>	LC/UPC
<b>Rack Units</b>	1
<b>Total Ports, quantity</b>	24

### Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	355.6 mm   14 in

### Material Specifications

<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate (PC)
----------------------	--

### Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	Austel   CE   CSA   UL

# 760193805 | 360-iP-INSTA-LC-4LS

---

## Packaging and Weights

**Packaging quantity** 1

**Weight, net** 2.948 kg | 6.5 lb

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system

