

RH0056-000 | TRAC-D-BOLTED-KIT

TRAC Copper Closure, unpressurized, gel sealed, 22 inch sheath opening, 33 inch long



- Toolless, extendable and re-enterable closure for freebreathing aerial applications
- Consists of three main components: a central body and two end pieces and self support bond system
- Unique convoluted design provides both mechanical and environmental protection
- Recommended for use on polyethylene insulated cable jackets for straight and branch configurations

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	Latin America North America
Product Type	Gel sealed closure
Product Series	TRAC

General Specifications

Application	For use with Polyethylene cables
Cable Capacity, maximum	3
Cable Sealing Type	Gel filled
Closure Style	In-line
Color	Black
Mounting	Strand
Splicing Capacity, maximum	1800

Dimensions

Length	838.2 mm 33 in
Single Cable Diameter, maximum	83.82 mm 3.3 in
Splice Bundle Diameter, maximum	304.8 mm 12 in
Sheath Opening, nominal	558.8 mm 22 in

RH0056-000 | TRAC-D-BOLTED-KIT

Environmental Specifications

Environmental Space Aerial

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

