


# FFWLCSC21

## Base Product



TeraSPEED® LC/UPC to SC/UPC, Fiber Patch Cord, 1.6 mm Simplex, LSZH

## Product Classification

|                              |  |
|------------------------------|--|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   Europe   Latin America   Middle East /Africa   North America                              |
| <b>Portfolio</b>             | CommScope®   |
| <b>Product Type</b>          | Fiber patch cord, simplex  |
| <b>Product Brand</b>         | SYSTIMAX InstaPATCH® 360   |
| <b>Product Series</b>        | FFW  |
| <b>Ordering Note</b>         | For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration |

## General Specifications


|                               |        |
|-------------------------------|--------|
| <b>Color, connector A</b>     | Blue   |
| <b>Color, connector B</b>     | Blue   |
| <b>Interface, Connector A</b> | LC/UPC |
| <b>Interface, Connector B</b> | SC/UPC |
| <b>Total Fibers, quantity</b> | 1      |

## Dimensions

|   |                   |
|---|-------------------|
| <b>Cable Assembly Length Range (m)</b>  | 1 – 999           |
| <b>Cable Assembly Length Range (ft)</b> | 1 – 999           |
| <b>Diameter Over Jacket</b>             | 1.6 mm   0.063 in |

## Ordering Tree

# FFWLCSC21



## Mechanical Specifications

**Cable Retention Strength, maximum** 11.24 lb @ 0 ° | 4.40 lb @ 90 °

## Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.652.D | G.657.A1, TeraSPEED®

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Environmental Space** Dual Rated LSZH/Riser

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |



## Included Products

- 460125743 – TeraSPEED® Pre-Radiused SC Connector for 1.6 mm Fiber Cordage, Simplex, Singlemode
- 760164160 – Fiber Indoor Cable, OptiSPEED® 1.6mm Low Smoke Zero Halogen Riser, 1-fiber Simplex, Singlemode G.652.D and G.657.A1, Yellow jacket color, Eca Flame Rating
- N-001-SP-8W-F16YL/E

# 460125743

---

## TeraSPEED® Pre-Radiused SC Connector for 1.6 mm Fiber Cordage, Simplex, Singlemode

### Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber connector   |
| <b>Product Brand</b>         | TeraSPEED®  |

### General Specifications

|                         |              |
|-------------------------|--------------|
| <b>Body Style</b>       | Simplex      |
| <b>Color</b>            | Blue         |
| <b>Ferrule Geometry</b> | Pre-radiused |
| <b>Interface</b>        | SC/UPC       |

### Dimensions

|                                  |                   |
|----------------------------------|-------------------|
| <b>Length</b>                    | 56 mm   2.205 in  |
| <b>Compatible Cable Diameter</b> | 1.6 mm   0.063 in |

### Material Specifications

|                         |          |
|-------------------------|----------|
| <b>Ferrule Material</b> | Zirconia |
|-------------------------|----------|

### Mechanical Specifications

|  |                |
|--|----------------|
| <b>Cable Retention Strength, maximum</b> | 11.24 lb @ 0 ° |
|--|----------------|

### Optical Specifications

|   |  |
|---|--|
| <b>Fiber Type</b>                         | G.652.D and G.657.A1, TeraSPEED®   OS2 |
| <b>Insertion Loss Change, mating</b>      | 0.3 dB                                 |
| <b>Optical Components Standard</b>        | ANSI/TIA-568-C.3                       |
| <b>Insertion Loss Change, temperature</b> | 0.3 dB                                 |
| <b>Insertion Loss, typical</b>            | 0.3 dB                                 |
| <b>Return Loss, minimum</b>               | 55 dB                                  |

### Packaging and Weights

# 460125743

---

**Packaging quantity**

1

## Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant




## \* Footnotes

**Insertion Loss Change, mating**

TIA-568: Maximum insertion loss change after 500 matings

**Insertion Loss Change, temperature**

Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)



Fiber Indoor Cable, OptiSPEED® 1.6mm Low Smoke Zero Halogen Riser, 1-fiber Simplex, Singlemode G.652.D and G.657.A1, Yellow jacket color, Eca Flame Rating

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber indoor cable  |
| <b>Product Series</b>        | N-SP  |


## General Specifications

|                          |             |
|--------------------------|-------------|
| <b>Cable Type</b>        | Cordage     |
| <b>Construction Type</b> | Non-armored |
| <b>Subunit Type</b>      | Gel-free    |
| <b>Jacket Color</b>      | Yellow      |
| <b>Jacket Marking</b>    | Feet        |
| <b>Total Fiber Count</b> | 1           |

## Dimensions

|                             |                   |
|-----------------------------|-------------------|
| <b>Diameter Over Jacket</b> | 1.7 mm   0.067 in |
|-----------------------------|-------------------|

## Representative Image



## Mechanical Specifications

|  |                                       |
|--|---------------------------------------|
| <b>Minimum Bend Radius, loaded</b>       | 38 mm   1.496 in                      |
| <b>Minimum Bend Radius, unloaded</b>     | 15 mm   0.591 in                      |
| <b>Tensile Load, long term, maximum</b>  | 29 N   6.519 lbf                      |
| <b>Tensile Load, short term, maximum</b> | 98 N   22.031 lbf                     |
| <b>Compression</b>                       | 10 N/mm   57.101 lb/in                |
| <b>Compression Test Method</b>           | FOTP-41   IEC 60794-1 E3              |
| <b>Flex</b>                              | 300 cycles                            |
| <b>Flex Test Method</b>                  | FOTP-104   IEC 60794-1 E6             |
| <b>Impact</b>                            | 0.74 N-m   6.55 in lb                 |
| <b>Impact Test Method</b>                | FOTP-25   IEC 60794-1 E4              |
| <b>Strain</b>                            | See long and short term tensile loads |
| <b>Strain Test Method</b>                | FOTP-33   IEC 60794-1 E1              |
| <b>Twist</b>                             | 10 cycles                             |
| <b>Twist Test Method</b>                 | FOTP-85   IEC 60794-1 E7              |
| <b>Vertical Rise, maximum</b>            | 500 m   1,640.42 ft                   |

## Optical Specifications

|                   |                                  |
|-------------------|----------------------------------|
| <b>Fiber Type</b> | G.652.D and G.657.A1, TeraSPEED® |
|-------------------|----------------------------------|

## Environmental Specifications

# 760164160 | N-001-SP-8W-F16YL/E

|   |   |
|---|---|
| <b>Installation temperature</b>                     | -20 °C to +60 °C (-4 °F to +140 °F)   |
| <b>Operating Temperature</b>                        | -20 °C to +70 °C (-4 °F to +158 °F)   |
| <b>Storage Temperature</b>                          | -40 °C to +70 °C (-40 °F to +158 °F)  |
| <b>Cable Qualification Standards</b>                | ANSI/ICEA S-83-596   Telcordia GR-409                                       |
| <b>EN50575 CPR Cable EuroClass Fire Performance</b> | Eca   |
| <b>Environmental Space</b>                          | Low Smoke Zero Halogen (LSZH)   Riser                                       |
| <b>Flame Test Listing</b>                           | NEC OFNR-ST1 (ETL) and c(ETL)   |
| <b>Flame Test Method</b>                            | IEC 60332-1-2   IEC 60332-3   IEC 60754-2   IEC 61034-2   UL 1666   UL 1685 |

## Environmental Test Specifications

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| <b>Heat Age</b>                      | -20 °C to +85 °C (-4 °F to +185 °F) |
| <b>Heat Age Test Method</b>          | IEC 60794-1 F9                      |
| <b>Low High Bend</b>                 | -20 °C to +70 °C (-4 °F to +158 °F) |
| <b>Low High Bend Test Method</b>     | FOTP-37   IEC 60794-1 E11           |
| <b>Temperature Cycle</b>             | -20 °C to +70 °C (-4 °F to +158 °F) |
| <b>Temperature Cycle Test Method</b> | FOTP-3   IEC 60794-1 F1             |

## Packaging and Weights

|                     |                          |
|---------------------|--------------------------|
| <b>Cable weight</b> | 2.8 kg/km   1.882 lb/kft |
|---------------------|--------------------------|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CENELEC       | EN 50575 compliant, Declaration of Performance (DoP) available   |
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |



## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable