

MONITOR 4



Monitor Free Cooling System, 4 kW

- Reduces energy consumption and CO² emissions in excess of 90%
- Recoups investment in one to three years
- Can be used as a direct cooling system or to work with existing air conditioning installation
- Comprehensive alarms alert to issues with the system or the cabinet environment
- Real time and online telemetry and control

Product Classification

Product Type Cooling system

General Specifications

Color Standard RAL Colors available

Cooling Capacity at $\Delta t=10$ °C (inlet to exhaust) 4.5 W

Cooling Capacity at $\Delta t=7$ °C (inlet to exhaust) 3.2 W

Fans, quantity 2

Flow Rate at 100% Fan Speed 1500 m³/hr

Installation Duration 4 hrs

Installation Team, quantity 2

Dimensions

Height 610 mm | 24.016 in

Width 520 mm | 20.472 in

Depth 195 mm | 7.677 in

Electrical Specifications

Operating Current at Voltage, maximum 6.8 A @-52 Vdc

Power Consumption at 50% Speed 44 W

Power Consumption at Nominal Voltage 350 W

Voltage -38 Vdc | -58 Vdc

Material Specifications

Finish Powder coated

Material Type Galvanized steel

MONITOR 4

Environmental Specifications

Operating Temperature	-30 °C to +40 °C (-22 °F to +104 °F)
Air Filtration Efficiency	MERV 11
Qualification Standards	CE

Packaging and Weights

Weight, net	65 kg 143.3 lb
--------------------	------------------