## UNXMPLUCG

#### **Base Product**



Ultra Low Loss ULL LazrSPEED® 550 MPO(Unpinned) to LC/UPC Uniboot Ruggedized fanout Cable, 36-Fiber, LSZH, 12 fiber PmP 2.0 mm Dca

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle

East/Africa | North America

Portfolio CommScope®

Product Type Ruggedized fanout

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

### General Specifications

Color, boot A Black

Color, connector A Black

Color, boot B Blue

Color, connector B Black

Construction Type Stranded

Furcation Color Aqua

Interface, Connector A MPO-12/UPC Female

Interface, Connector B LC/UPC

Interface Feature, connector B Uniboot

**Jacket Color** Aqua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 36

**Dimensions** 


Cable Assembly Length Range (m) 3 – 999

## UNXMPLUCG

#### Cable Assembly Length Range (ft)

10 - 999

## Ordering Tree



## **Optical Specifications**

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

### **Environmental Specifications**

**Operating Temperature**  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

EN50575 CPR Cable EuroClass Fire Performance Dca

Environmental Space Dual Rated LSZH/Riser | Indoor

Regulatory Compliance/Certifications

# UNXMPLUCG

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### Included Products

760227231 – Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 36 fiber multi-unit N-036-MP-5K-F12AQ/20T/D with 12 fiber 2.0mm subunits, Gel-free, Multimode OM4, Feet jacket marking, Aqua jacket color,

Dca flame rating

860658161 – 2.0 mm LC/UPC Uniboot GEN 1.5, Aqua 860659012 – MPO12, ULL, FEMALE, OM3/4, AQUA, 2MM



# 760227231 | N-036-MP-5K-F12AQ/20T/D



Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 36 fiber multi-unit with 12 fiber 2.0mm subunits, Gel-free, Multimode OM4, Feet jacket marking, Aqua jacket color, Dca flame rating

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

Product Series N-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

**Subunit Type** Gel-free

**Jacket Color** Aqua

Jacket Marking Feet

Subunit, quantity 3

Fibers per Subunit, quantity 12

Total Fiber Count 36

**Dimensions** 

Buffer Tube/Subunit Diameter2 mm0.079 inDiameter Over Jacket7 mm0.276 in

Representative Image



# 760227231 | N-036-MP-5K-F12AQ/20T/D

200 N | 44.962 lbf



### Mechanical Specifications

Tensile Load, long term, maximum

Minimum Bend Radius, loaded 105 mm | 4.134 in

Minimum Bend Radius, unloaded 70 mm | 2.756 in

**Tensile Load, short term, maximum** 667 N | 149.948 lbf

**Compression** 10 N/mm | 57.101 lb/in

**Compression Test Method** FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

FIEX Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 387 m | 1,269.685 ft

**Optical Specifications** 

Fiber Type OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

### **Environmental Specifications**

Installation temperature  $0 \, ^{\circ}\text{C} \, \text{to} + 60 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} + 140 \, ^{\circ}\text{F})$ Operating Temperature  $0 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ Storage Temperature  $-40 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ 

Page 5 of 10



# 760227231 | N-036-MP-5K-F12AQ/20T/D

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Rating\$1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

**Environmental Test Specifications** 

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-20 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-4 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )Low High Bend Test MethodFOTP-37 | IEC 60794-1 E11Temperature Cycle $0 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $+32 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 47.4 kg/km | 31.851 lb/kft

#### Regulatory Compliance/Certifications

#### Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



#### 2.0 mm LC/UPC Uniboot GEN 1.5, Aqua

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

**Product Type** Fiber connector boot

### General Specifications

ColorAquaCompatible InterfaceLCFerrule GeometryFlat

**Dimensions** 

**Compatible Cable Diameter** 2 mm | 0.079 in

#### Optical Specifications

Fiber Mode Multimode

**Fiber Type** OM4

Attenuation, nominal0.13 dBInsertion Loss, maximum0.15 dBReturn Loss, minimum35 dB

### Packaging and Weights

Packaging Type Bag

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

**UK-ROHS** 

Compliant







#### MPO12, ULL, FEMALE, OM3/4, AQUA, 2MM

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

ColorAquaColor, bootBlackFerrule GeometryFlat

Interface MPO/UPC Female

Interface Feature Unpinned

**Total Fiber Count** 12

**Dimensions** 

Length 60.1 mm | 2.366 in Compatible Cable Diameter 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 ^{\circ}$ 

Optical Specifications

**Fiber Mode** Singlemode

Fiber Type OM3, LazrSPEED® | OM4, LazrSPEED®

Insertion Loss Change, mating 0.2 dB

Optical Components Standard ANSI/TIA-568-C.3

 Insertion Loss, maximum
 0.2 dB

 Return Loss, minimum
 27 dB

Packaging and Weights

Packaging quantity 1

\* Footnotes

Insertion Loss Change, mating TIA-568: Maximum insertion loss change after 500 matings

